



**Product:** [TT-SLC-006-LSN](#)

Transit, In+Outdoor, MLT, OS2, 6f, Dry Tubes 2.5mm, CST, Sgl Jkt, Blk, LSZH, OFCG-ST1

**Product Description**

Transit Grade, Indoor/Outdoor, Multi-Loose-Tube, OS2, 6 Fibers, Dry Tubes 2.5mm, Corrugated Steel Tape, Single Jacket, Black, LSZH, OFCG-ST1

**Technical Specifications**

**Product Overview**

|                        |   |
|------------------------|---|
| Product Category:      | Fiber Multi-Loose Tube Cable  |
| Suitable Applications: | Extended Distance Horizontal & Backbone Data/Telco Network, Noisy Environment, Indoor/ Outdoor & Wet Locations, Armored, UV Resistant |

**Fiber Specifications**

|                      |            |
|----------------------|------------|
| Fiber Type:          | OS2        |
| Fiber Core Diameter: | 8.2/125 µm |
| Fiber Diameter:      | 250 µm     |
| Fiber Color Coding:  | TIA-598-D  |

**Cable Construction**

|                            |                   |
|----------------------------|-------------------|
| Number of Active Subunits: | 1                 |
| Number of Fillers:         | 4                 |
| Fibers Per Subunit:        | 6                 |
| Subunit Waterblocking:     | Gel Free          |
| Subunit Diameter:          | 0.098 in (2.5 mm) |
| Subunit Color:             | TIA-598-D         |
| Central Strength Member:   | GRP               |

**Armor Specifications**

|                          |                             |
|--------------------------|-----------------------------|
| Armor Type and Material: | CST - Corrugated Steel Tape |
|--------------------------|-----------------------------|

**Outer Jacket Specifications**

|                     |   |
|---------------------|---|
| Strength Member:    | Fiberglass Yarns                                |
| Jacket Material:    | LSZH - Low Smoke Zero Halogen (Flame Retardant) |
| Nom. Diameter:      | 0.530 in (13.5 mm)                              |
| Number of Ripcords: | 2   |

**Optical Characteristics**

| Wavelength                      | 1310 nm | 1550 nm |
|---------------------------------|---------|---------|
| Max. Attenuation                | 0.35    | 0.25    |
| Mode Field Diameter             | 9.2 µm  | 10.4 µm |
| 1 Gigabit Ethernet Performance  | 5000 m  |         |
| 10 Gigabit Ethernet Performance | 10000 m | 40000 m |

**Mechanical Characteristics**

|  |                  |
|--|------------------|
| Min. Bend Radius During Installation:      | 20x Cable OD     |
| Min. Bend Radius During Operation:         | 10x Cable OD     |
| Max. Tensile Strength During Installation: | 2670 N (600 lbf) |

|   |                         |
|---|-------------------------|
| Max. Tensile Strength During Operation: | 800 N (180 lbf)         |
| Crush Resistance:                       | 220 N/cm                |
| Bulk Cable Weight:                      | 129 lbs/kft (192 kg/km) |

## Temperature Range

|                                 |                |
|---------------------------------|----------------|
| Installation Temperature Range: | -10°C to +60°C |
| Operating Temperature Range:    | -40°C to +70°C |
| Storage Temperature Range:      | -40°C to +70°C |

## Standards and Compliance

|                                  |   |
|----------------------------------|---|
| Environmental Suitability:       | Indoor/Outdoor, Sunlight Resistance, Burial |
| Flammability / Reaction to Fire: | UL 1685 FT4 Loading, Limited Smoke, FT4     |
| NEC / UL Compliance:             | OFCG-ST1                                    |
| ICEA Compliance:                 | S-104-696                                   |

## History

|                      |  |
|----------------------|--|
| Update and Revision: | Revision Number: 0.9 Revision Date: 11-14-2022 |
|----------------------|--|

## Part Numbers

### Variants

| Item #          |
|-----------------|
| TT-SLC-006-LSNN |

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.