


1694S5 Coax - VideoFLEX® Snake Cables for Precision Analog & Digital Video



For more Information
please call

1-800-Belden1



General Description:

18 AWG solid .040" bare copper conductors, gas-injected foam HDPE insulation, Duofoil® (100% coverage) plus a tinned copper braid shield (95% coverage), individual PVC jackets.

Usage (Overall)

Suitable Applications: RGB, VGA, SVGA, XGA, SXGA, UXGA, HDTV, LCD, Plasma, Digital Signage, Component Video, Video Mult, Animation, Special Effects, Suitable for use in Risers

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
5	18	Solid	BC - Bare Copper	1.016

Total Number of Conductors: 5

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FHDPE - Foam High Density Polyethylene	4.572

Inner Shield

Inner Shield Material:

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (mm)
PVC - Polyvinyl Chloride	6.9596

Inner Jacket Color Code Chart:

Number	Color
1	Red
2	Green
3	Blue
4	White
5	Yellow

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
Unjacketed

Overall Cable

Overall Cabling Fillers: Bonded Spline

Overall Nominal Diameter: 18.796 mm

Mechanical Characteristics (Overall)

METRIC MEASUREMENT VERSION

1694S5 Coax - VideoFLEX® Snake Cables for Precision Analog & Digital Video

Operating Temperature Range:	-35°C To +75°C
UL Temperature Rating:	60°C
Non-UL Temperature Rating:	75°C
Bulk Cable Weight:	349.727 Kg/Km
Max. Recommended Pulling Tension:	1601.350 N
Min. Bend Radius/Minor Axis:	203.200 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	6/U

Applicable Patents:

Country
www.belden.com/p

Flame Test

UL Flame Test:	UL1666 Vertical Shaft
----------------	-----------------------

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Inductance:

Inductance (µH/m)
0.351067

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)
53.1522

Nominal Velocity of Propagation:

VP (%)
82

Nominal Delay:

Delay (ns/m)
4.06844

Nom. Conductor DC Resistance:

METRIC MEASUREMENT VERSION

1694S5 Coax - VideoFLEX® Snake Cables for Precision Analog & Digital Video

DCR @ 20°C (Ohm/km)

20.9984

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/km)

9.1868

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1.000	0.787
3.580	1.444
5.000	1.706
7.000	2.001
10.000	2.330
67.500	5.414
71.500	5.545
88.500	6.103
100.000	6.398
135.000	7.349
143.000	7.546
180.000	8.432
270.000	10.401
360.000	12.107
540.000	15.093
720.000	17.652
750.000	18.046
1000.000	21.064
1500.000	26.215
2000.000	30.743
2250.000	32.843
3000.000	38.650
4500.000	48.953

Max. Operating Voltage - UL:

Voltage

300 V RMS

Other Electrical Characteristic 1:

Impedance tested in accordance with ASTM D-4566 paragraph 43.2, option 2 using a 75 Ohm fixed bridge and termination.

Other Electrical Characteristic 2:

Return Loss Tested in Accordance With ASTM D-4566 Paragraph 45.3, Using a 75 Ohm Fixed Bridge and Termination.

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5	435	20
435	515	15
515	1600	20
1600	4500	15

Sweep Test

Sweep Testing:

Sweep tested 5 MHz to 4.5 GHz.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 2 Revision Date: 02-28-2014

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express,

METRIC MEASUREMENT VERSION

1694S5 Coax - VideoFLEX® Snake Cables for Precision Analog & Digital Video

statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).