

## 19126 Portable Cordage - UL/CSA Types: SPT-1, SPT-2, SP-1 and HPN

For more Information  
please call

1-800-Belden1



### General Description:

SPT-2 PVC parallel lamp cord, UL/CSA listed, 300V 60°C, one conductor polarity ribbed.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

| # Conductors | AWG | Stranding | Conductor Material |
|--------------|-----|-----------|--------------------|
| 2            | 16  | 65x34     | BC - Bare Copper   |

Total Number of Conductors: 2

Type of Cordage: SPT-2

#### Insulation

##### Insulation Material:

| Insulation Material      | Wall Thickness (mm) |
|--------------------------|---------------------|
| PVC - Polyvinyl Chloride | 1.2192              |

#### Outer Shield

##### Outer Shield Material:

| Outer Shield Material |
|-----------------------|
| Unshielded            |

#### Overall Cable

Overall Nominal Diameter: 3.937 x 7.595 mm

### Mechanical Characteristics (Overall)

UL Temperature Rating: 60°C

Bulk Cable Weight: 52.087 Kg/Km

Min. Bend Radius/Minor Axis: 44.450 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: SPT-2

CSA Specification: SPT-2

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

#### Flame Test

METRIC MEASUREMENT VERSION

## 19126 Portable Cordage - UL/CSA Types: SPT-1, SPT-2, SP-1 and HPN

CSA Flame Test: FT2

### Plenum/Non-Plenum

Plenum (Y/N): No

### Surface Printing (Overall)

Surface Printing: "16-2 SPT-2 60°C (UL) E3462 - - - - CSA LL-7874 16-2 SPT-2 60°C FT2"

### Electrical Characteristics (Overall)

#### Max. Operating Voltage - UL:

##### Voltage

300 V RMS

#### Max. Recommended Current:

##### Current

13 Amps per conductor @ 25°C

10 Amps per conductor @ 25°C (over 50 ft.)

Dielectric Withstand Voltage: 1500 V AC Applied for 1 Min.

### Put Ups and Colors:

| Item #       | Putup  | Ship Weight | Color | Notes | Item Desc          |
|--------------|--------|-------------|-------|-------|--------------------|
| 19126 010250 | 250 FT | 9.750 LB    | BLACK | F     | 2 #16 PVC PARALLEL |

#### Notes:

F = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'

Revision Number: 2    Revision Date: 11-02-2012

© 2019 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).