

2141A Multi-Conductor - Category 6A Indoor/Outdoor OSP/CM-LS F/UTP LSZH Cable



For more Information
please call

1-800-Belden1



General Description:

CAT6A (500 MHz), 4 Pair, F/UTP-Foil Shielded, Indoor/Outdoor OSP/CM-LS, Premise Horizontal Cable, 23 AWG Solid Bare Copper Conductors, Polyolefin Insulation, Patented X-Spline, Gel-Filled, Haloarrest® LSZH Inner Jacket, Overall Beldfoil® Shield with Drain Wire, Ripcord, UV-Resistant Flame Retardant Haloarrest® LSZH Outer Jacket

Usage (Overall)

Suitable Applications: OSP, CM-LS, Outside Plant Cable, 10 Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments, PoE, PoE+

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	23	Solid	BC - Bare Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material
Polyolefin

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)	Dia. (mm)
Beldfoil	Bi-Laminate	polyester/foil	100.000	6.858

Inner Shield Drain Wire AWG:

AWG	Stranding	Dia. (mm)	Conductor Material
26	7X34	0.483	TC

Inner Jacket

Inner Jacket Material:

Inner Jacket Material
Haloarrest(R) LSZH

Inner Jacket Ripcord: Yes

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
Haloarrest(R) LSZH

Outer Jacket Diameter:

Nom. Dia. (mm)
9.144

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Separator Material: Patented X-Spline Center Member

2141A Multi-Conductor - Category 6A Indoor/Outdoor OSP/CM-LS F/UTP LSZH Cable

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-20°C To +75°C
Operating Temperature Range:	-20°C To +70°C
UL Temperature Rating:	75C
Non-UL Temperature Rating:	60C
Bulk Cable Weight:	98.221 Kg/Km
Max. Recommended Pulling Tension:	200.169 N
Min. Bend Radius/Minor Axis:	76.200 mm
Min. Bend/Installation:	95.250 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM-LS
CEC/C(UL) Specification:	CM-LS
EU Directive 2011/65/EU (ROHS II):	Yes
IEEE Specification:	POE per IEEE 802.3af & POE+ per IEEE 802.3at-2009
Other Standards:	ISO/IEC 11801 ed 2 Amendment 2:2010 Class EA
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	03/07/2011
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	ISO/IEC 11801:2011 Amendment 2.2 Class EA
ANSI Specification:	ANSI/TIA 568-C.2 Category 6A, ANSI/ICEA S-116-732-2013 Category 6A, ANSI/NEMA WC-63.1 Category 6A
Other Specification:	ANSI/ICEA S-56-434 Outdoor Use, ANSI/ICEA S-99-689 Broadband Outdoor Use, Indoor/Outdoor Use ANSI/ICEA S-100-685

Applicable Patents:

Country
www.belden.com/p

Flame Test

UL Flame Test:	UL1581 Vertical Tray, UL1685 Vertical Tray Flame Test
C(UL) Flame Test:	Limited Smoke
CSA Flame Test:	Limited Smoke
IEC Flame Test:	60332-1

2141A Multi-Conductor - Category 6A Indoor/Outdoor OSP/CM-LS F/UTP LSZH Cable

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Aerial:	Yes - When supported by messenger wire
Suitability - Burial:	Yes
Suitability - Hazardous Locations:	No
Sunlight Resistance:	Yes
Non-halogenated:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	10GX53F
Non-Plenum Number:	10GX52F

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/m)
55.777

Maximum Capacitance Unbalance (pF/100 m): 45

Nominal Velocity of Propagation:

VP (%)
64.000

Maximum Delay:

Delay (ns/100 m)
538 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m)
45.000

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
8.200

Max. Operating Voltage - UL:

Voltage
300 V RMS

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. PSNEXT (dB)	Min. PSACR (dB)	Min RL (dB)
1	2.100	72.3	70.2	20.000
4	3.800	63.3	59.5	23.000
8	5.300	58.8	53.4	24.500
10	5.900	57.3	51.4	25.000
16	7.500	54.2	46.8	25.000
20	8.400	52.8	44.5	25.000
25	9.400	51.3	42.0	24.300
31.25	10.500	49.9	39.4	23.600
62.5	15.000	45.4	30.4	21.500
100	19.100	43.3	23.2	20.100
200	27.600	37.8	10.2	18.700
250	31.100	36.3	5.3	18.000
300	34.300	35.1	0.9	17.500
350	37.200	34.1	N/A	17.000
400	40.100	33.3	N/A	16.600

2141A Multi-Conductor - Category 6A Indoor/Outdoor OSP/CM-LS F/UTP LSZH Cable

450	42.700	32.5	N/A	16.200
500	45.300	31.8	N/A	15.900

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ACRF (dB)	Min. PSACRF (dB)
1	105 ± 10	115 ± 15	67.8	64.8
4	105 ± 10	100 ± 7	55.8	52.8
8	100 ± 22	100 ± 7	49.7	46.7
10	100 ± 22	100 ± 7	47.8	44.8
16	100 ± 22	100 ± 7	43.7	40.7
20	100 ± 22	100 ± 7	41.8	38.8
25	100 ± 22	100 ± 7	39.8	36.8
31.25	100 ± 22	100 ± 7	37.9	34.9
62.5	100 ± 22	100 ± 7	31.9	28.9
100	100 ± 22	100 ± 7	27.8	24.8
200	100 ± 32	100 ± 7	21.8	18.8
250	100 ± 32	100 ± 7	19.8	16.8
300	100 ± 32	100 ± 7	18.3	15.3
350	100 ± 32	100 ± 7	16.9	13.9
400	100 ± 32	100 ± 7	15.8	12.8
450	100 ± 32	100 ± 7	14.7	11.7
500	100 ± 32	100 ± 7	13.8	10.8

Premise Cable Electrical Table 4:

Frequency (MHz)	Min. PSANEXT (dB)	Min. PSAACRF (dB)	Min. TCL (dB)	Min. ELTCTL (dB)
1.000	67.000	67.000	40.000	35.000
4.000	67.000	66.200	40.000	23.000
8.000	67.000	60.100	40.000	16.900
10.000	67.000	58.200	40.000	15.000
16.000	67.000	54.100	38.000	10.900
20.000	67.000	52.200	37.000	9.000
25.000	67.000	50.200	36.000	7.000
31.250	67.000	48.300	35.100	5.100
62.500	65.600	42.300	32.000	
100.000	62.500	38.200	30.000	
200.000	58.000	32.200	27.000	
250.000	56.500	30.200	26.000	
300.000	55.300	28.700	25.300	
350.000	54.300	27.300	24.600	
400.000	53.500	26.200	24.000	
450.000	52.700	25.100	23.500	
500.000	52.000	24.200	23.000	

Notes (Overall)

Notes: Third party channel verified to and meets component requirements of TIA/EIA-568-C.2, Category 6A, Print Includes Descending Footage / Meter Markings, -20C Cold Bend Compliance Per UL1581, Reference T/8-6 for Burial, T/8/36 for Sag and Span Aerial, Water Penetration per GR 421-CORE para. 4.3.5.1, ANSI/ICEA S-107-704 Para. 8.2.1 and ICEA S-99-689

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
2141A 0101000	1,000 FT	53.000 LB	BLACK		CAT6A 4PR F/UTP OSP-CM REEL

Revision Number: 2 Revision Date: 08-01-2017

© 2020 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract,

METRIC MEASUREMENT VERSION

2141A Multi-Conductor - Category 6A Indoor/Outdoor OSP/CM-LS F/UTP LSZH Cable

negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).