



For more Information
please call

1-800-Belden1



General Description:

CMP, FPLP, 2-20 AWG solid bare copper pairs with Flamarrest® PVC insulation, Beldfoil® shield and Flamearrest® PVC jacket with ripcord

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
2	20	Solid	BC - Bare Copper

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
Flamarrest® PVC	0.254

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Outer Shield Material
Beldfoil®	Aluminum Foil-Polyester Tape

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	7x32	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
Flamarrest® PVC	0.381

Overall Cable

Overall Nominal Diameter: 5.613 mm

Pair

Pair Color Code Chart:

Number	Color
1	Red & Red
2	Black & Black

Mechanical Characteristics (Overall)

Operating Temperature Range: 0°C To +75°C

Bulk Cable Weight: 25.299 Kg/Km

Max. Recommended Pulling Tension: 145.011 N

Min. Bend Radius/Minor Axis: 55.880 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP, FPLP

2152PE Multi-Conductor - Commercial Applications

EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL910 Steiner Tunnel
----------------	----------------------

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Surface Printing (Overall)

Surface Printing:	BELDEN 2152PE E64959 (-PLANT ID) 20AWG 2PR SHIELDED (UL) TYPE FPLP OR CMP C(UL) (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FT
-------------------	--

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)
200.797

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
111.554

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
33.7943

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
34.4505

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
2.6 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
2152PE 0021000	1,000 FT	27.000 LB	RED		2 PR #20 FLRST FS FLRST

Revision Number: 0 Revision Date: 03-14-2014

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

2152PE Multi-Conductor - Commercial Applications

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).