

27292 Multi-Conductor - 600V Type MC Metal Clad Cable



For more Information
please call

1-800-Belden1



General Description:

14 AWG stranded (7x22) bare copper conductors, 14 AWG bare copper ground wire, cross-linked polyethylene insulation, aluminum interlocked armor, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
37	14	7x22	BC - Bare Copper

Total Number of Conductors: 37

Ground Wire

Ground Wire (Y/N): Y

Ground Wire AWG: 14

Ground Wire Stranding: 7x22

Ground Wire Conductor Material: BC - Bare Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
XLPE - Cross Linked Polyethylene	0.762

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket over Armor (y/n): Y

Outer Jacket over Armor

Outer Jacket Material over Armor (y/n): PVC

Outer Jacket Wall Thickness Over Armor: .050

Armor

Armor Type: Interlocked

Armor Material: Aluminum

Diameter over Armor: 1.14

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red
3	Blue
4	Orange
5	Yellow
6	Brown
7	Red/Black

27292 Multi-Conductor - 600V Type MC Metal Clad Cable

8	Blue/Black
9	Orange/Black
10	Yellow/Black
11	Brown/Black
12	Black/Red
13	Blue/Red
14	Orange/Red
15	Yellow/Red
16	Brown/Red
17	Black/Blue
18	Red/Blue
19	Orange/Blue
20	Yellow/Blue
21	Brown/Blue
22	Black/Orange
23	Red/Orange
24	Blue/Orange
25	Yellow/Orange
26	Brown/Orange
27	Black/Yellow
28	Red/Yellow
29	Blue/Yellow
30	Orange/Yellow
31	Brown/Yellow
32	Black/Brown
33	Red/Brown
34	Blue/Brown
35	Orange/Brown
36	Yellow/Brown
37	Black

Overall Nominal Diameter: 31.496 mm

Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +90°C
Wet Temperature Range:	-40°C To +90°C
Dry Temperature Range:	-40°C To +90°C
Bulk Cable Weight:	1534.330 Kg/Km
Max. Recommended Pulling Tension:	5293.360 N
Min. Bend Radius/Minor Axis:	408.940 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC(UL) Specification:	MC, XHHW-2 Singles, UL1569
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/13/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test: UL1685 UL Loading

Suitability

Suitability - Burial: Yes

Sunlight Resistance: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

8.5306

Max. Operating Voltage - UL:

Voltage

600 V RMS

Max. Recommended Current:

Current

6 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 1 Revision Date: 05-14-2007

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.