



Product: [Triangular Support Bkt - Steel](#)



Triangular Support Bracket, Steel

Product Description

Triangular Support Bracket - Steel

Technical Specifications

Application

Product Overview:	Provides wall support for cable runway. Made of cold-rolled steel.
Benefits:	Provides wall support for cable runway., Made of cold-rolled steel.
Environmental Space:	Indoor

Mechanical Characteristics

Load Capacity:	400 lb
----------------	--------

Environmental and Overall Characteristics

Finish:	Black Powdercoat Finish
Material:	Steel
Color:	Black

Related Part Numbers

Included Parts:	Kit consists of: (1) vertical wall-mounting bracket, (1) runway support channel, (1) angle support channel, (3) clevis pins (5/16" diameter) & cotter pins, (2) 5/16"-18 x 2.25" J-bolts, (2) 5/16"-18 hex nuts & split washers
Packaging:	Individually Boxed

Variants

Part #	Description	Color	Included Parts	Shipping Weight
BLTSB746-12B	12" Triangular Support Bracket, Steel for use with 6" - 12"W Cable Runway	Black	Kit consists of: (1) vertical wall-mounting bracket, (1) runway support channel, (1) angle support channel, (3) clevis pins (5/16" diameter) & cotter pins, (2) 5/16"-18 x 2.25" J-bolts, (2) 5/16"-18 hex nuts & split washers	5.0 lb
BLTSB746-24B	24" Triangular Support Bracket, Steel for use with 24"W Cable Runway	Black	Kit consists of: (1) vertical wall-mounting bracket, (1) runway support channel, (1) angle support channel, (3) clevis pins (5/16" diameter) & cotter pins, (2) 5/16"-18 x 2.25" J-bolts, (2) 5/16"-18 hex nuts & split washers	9.0 lb
BLTSB746-18B	18" Triangular Support Bracket, Steel for use with 18"W Cable Runway	Black	Kit consists of: (1) vertical wall-mounting bracket, (1) runway support channel, (1) angle support channel, (3) clevis pins (5/16" diameter) & cotter pins, (2) 5/16"-18 x 2.25" J-bolts, (2) 5/16"-18 hex nuts & split washers	8.0 lb
Update and Revision:		Revision Number: 0.147 Revision Date: 11-14-2022		

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.