



Product: [UK1601BW](#)

Type KX Thermocouple, 1 Pr #16 Sol, XLPE Ins Yel, Red, OS, Yel LSZH Jkt, 600V TC 90C Dry/Wet SUN RES

Product Description

Type KX Thermocouple, 1 Pair 16AWG (Solid) Chromel+Alumel, XLPE Insulation Yel, Red Color Code, Overall Beldfoil® Shield, Yellow LSZH Outer Jacket, 600V TC 90C Dry/Wet SUN RES

Technical Specifications

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	Nominal Diameter	No. of Pairs
Pair(s)	16	Solid	Chromel & Alumel	0.051 in	1

Conductor Count:	2
------------------	---

Insulation

Element	Material	Nominal Diameter	Nominal Wall Thickness
Pair(s)	XLP, XLPO, XLPE (Thermoset)	0.113 in	0.031 in

Color Chart

Number	Color
1	Yellow
2	Red

Inner Shield

Drainwire Material	Drainwire Diameter	Drainwire AWG
TC - Tinned Copper	0.046 mm	18

Outer Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	0.046 in	18

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.324 in	0.047 in

Temperature Range

UL Temp Rating:	90°C
Operating Temperature Range:	-25°C To +90°C

Mechanical Characteristics

Bulk Cable Weight:	65 lbs/1000ft
Min Bend Radius (Overall):	3.25 in

Standards

NEC Articles:	Article 336
NEC/(UL) Compliance:	TC

ANSI Compliance:	MC 96.1-1982 Type KX
IEEE Compliance:	1202

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
CA Prop 65:	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

CSA Flammability:	FT4
IEEE Flammability:	1202
UL voltage rating:	600 V RMS (Type TC)

History

Update and Revision:	Revision Number: 0.47 Revision Date: 04-08-2022
----------------------	-------------------------------------------------

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.