



Product: [UTG20PCUP](#)

UTG 20 PATCHCORD, BONDED UTP, T568A/B, CMP

Product Description

UTG 20 PATCHCORD, BONDED UTP, T568A/B, CMP

Technical Specifications

Product Overview

Suitable Applications:	UTG 20, 10GBASE-T
------------------------	-------------------

Physical Characteristics (Overall)

Total Number of Pairs:	4
Overall Nominal Diameter:	0.255 in
Wiring Scheme:	T568A/B-T568A/B
Packaging:	Individually packaged in a clear plastic bag.

Connectors

Materials

Description	Material	Color
Boot	Elastomer	Translucent
Conductor	BC - Bare Copper	
Front Connection	Blades Phosphor Bronze with 50u inch Gold over Nickel Plating	
Inner Jacket	PVC - Polyvinyl Chloride	
Insulation	PO - Polyolefin	
Outer Jacket	PVC - Polyvinyl Chloride	

Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max Contact Resistance:	20 mOhm

Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Mechanical Characteristics

Min Bend Radius (Overall Cable):	1.040 in
Plug / Jack Compatibility:	RJ45

Termination Interface

Connection	Durabilities
Mated Connection	750 Cycles

Standards

UL Rating:	Plenum
Other Standards:	FCC Part 68, Subpart F, IEC 60603-7
Third Party Performance Verification:	UTG Framework 1.0, UTG Bear Attack (BERetAC)

Applicable Environmental and Other Programs

Environmental Space:	Plenum
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

Flammability, LSOH, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Product Notes

Labeling:	Belden Part Number, Performance Acronym, Wiring Scheme and Cord Length
-----------	--

History

Update and Revision:	Revision Number: 0.158 Revision Date: 07-10-2019
----------------------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.