



**Product:** [VersaLAN I/O OSP Cat 6 UTP](#)

Mohawk Category 6 Indoor/Outdoor Cable, 4 Pair, U/UTP, OSP/CM-LS, LSZH

**Product Description**

Mohawk Category 6 Premise Horizontal Cable, Indoor/Outdoor OSP/CM-LS, 4-Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Gel-filled, Haloarrest® UV Resistant Flame Retardant LSZH Jacket

**Technical Specifications**

**Product Overview**

Suitable Applications:	OSP-Outdoor, Indoor/Outdoor, Premise Horizontal Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, PoE++, PoE+, PoE, Noisy Environments: Not Suitable for Marine Application
------------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

**Construction Details**

**Conductor**

Size	Stranding	Material	No. of Pairs
23 AWG	Solid	BC - Bare Copper	4

**Insulation**

Material	Color Code
PO - Polyolefin	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Waterblocking:	Gel Filled
----------------	------------

**Outer Jacket**

Separator	Material	Nom. Diameter
Flexweb® Core Separator	LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.275 in (6.99 mm)

Overall Cable Diameter (Nominal):	0.275 in (6.99 mm)
-----------------------------------	--------------------

**Electrical Characteristics**

**Electricals**

Max. Conductor DCR	Max. Capacitance Unbalance
93.8 Ohm/km (28.6 Ohm/1000ft)	160 pF/100m

**Delay**

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
100 MHz	537.6 ns/100m	45 ns/100ft	65%

**High Frequency**

Frequency [MHz]	Max. Insertion Loss (Attenuation) [dB/100m]	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]	Max./Min. Fitted Impedance [Ohm]	Min. TCL [dB]	Min. ELTCTL [dB]
1	2.0	74.3	72.3	72.3	70.3	67.8	64.8	20.0	100 ± 15	100 ± 15	40.0	35.0
4	3.8	65.3	63.3	61.5	59.5	55.7	52.7	23.0	100 ± 15	100 ± 15	40.0	23.0
8	5.3	60.8	58.8	55.4	53.4	49.7	46.7	24.5	100 ± 15	100 ± 15	40.0	16.9
10	6.0	59.3	57.3	53.4	51.4	47.8	44.8	25.0	100 ± 15	100 ± 15	40.0	15.0
16	7.6	56.3	54.3	48.7	46.7	43.7	40.7	25.0	100 ± 15	100 ± 15	38.0	10.9
20	8.5	54.8	52.8	46.3	44.3	41.7	38.7	25.0	100 ± 15	100 ± 15	37.0	9.0
25	9.5	53.3	51.3	43.8	41.8	39.8	36.8	24.3	100 ± 15	100 ± 15	36.0	7.0

31.25	10.7	51.9	49.9	41.2	39.2	37.9	34.9	23.6	100 ± 15	100 ± 15	35.1	5.1
62.5	15.4	47.4	45.4	32.0	30.0	31.8	28.8	21.5	100 ± 15	100 ± 15	32.0	
100	19.8	44.3	42.3	24.5	22.5	27.8	24.8	20.1	100 ± 15	100 ± 15	30.0	
155	25.2	41.5	39.5	16.3	14.3	23.9	20.9	18.8	100 ± 22	100 ± 15	28.1	
200	29.0	39.8	37.8	10.8	8.8	21.7	18.7	18.0	100 ± 22	100 ± 15	27.0	
250	32.8	38.3	36.3	5.5	3.5	19.8	16.8	17.3	100 ± 32	100 ± 15	26.0	
500	48.9	33.8	31.8					15.2	100 ± 32	100 ± 15	23.0	
550	51.8	33.2	31.2					14.9	100 ± 32	100 ± 15	22.6	

#### Voltage

<b>UL Voltage Rating</b>
300 V (CM-LS)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating	Storage
60°C	-40°C To +60°C	-40°C To +60°C

#### Bend Radius

<b>Stationary Min.</b>
2.75 in (69.9 mm)

Max. Pull Tension:	25 lbs (11 kg)
Bulk Cable Weight:	39 lbs/1000ft (58 kg/km)

### Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Non-Halogenated, Sunlight Resistance, Aerial - Black only, When supported by messenger wire
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Reaction to Fire:	UL 1685 (UL Loading-Limited Smoke), IEC 60332-1-2
NEC / UL Compliance:	Article 800, CM-LS
CEC / C(UL) Compliance:	CMG-ST1
ICEA Compliance:	S-116-732, S-56-434, S-99-689, S-100-685
IEEE Compliance:	IEEE 802.3bt Type1, Type2, Type3, Type4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

### History

Update and Revision:	Revision Number: 0.39 Revision Date: 04-29-2024
----------------------	-------------------------------------------------

### Part Numbers

#### Variants

Item #	Color	Putup Type	Length
M58772	Black	Reel	1,000 ft
M59132	Blue	Reel	1,000 ft
M59092	White	Reel	1,000 ft

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.