



Product: [WireNet CAT5e Patch cord STP](#)

WireNet CAT5e Patch cord STP LSZH



Product Description

WireNet CAT5e Shielded LSZH Patch cord, 26AWG, Stranded

Technical Specifications

Product Overview

Suitable Applications:	Telecommunications Room, Main Distribution Room, Data Centers
------------------------	---

Physical Characteristics (Overall)

Wiring Scheme:	T568A/B-T568A/B
Packaging:	Individually packaged in a sealed plastic bag.

Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
----------------------	----------------------------------

Temperature Range

Operating Temperature Range:	-20°C to +60°C
------------------------------	----------------

Standards

Data Category:	Category 5e
TIA/EIA Compliance:	ISO/IEC 11801-1:2017; TIA 568-C.3

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

Related Part Numbers

Related Parts:	WireNet Jacks (CU-J....) , WireNet Panel (NN-UNIV-E) or KeyConnect empty panels (AX....)
----------------	--

Variants

Item #	Color	Length
CU-LPS5BK001M	Black	1 m
CU-LPS5BK002M	Black	2 m
CU-LPS5BK003M	Black	3 m
CU-LPS5BK004M	Black	4 m
CU-LPS5BK005M	Black	5 m
CU-LPS5BK007M	Black	7 m
CU-LPS5BL001M	Blue	1 m
CU-LPS5BL002M	Blue	2 m
CU-LPS5BL003M	Blue	3 m
CU-LPS5BL004M	Blue	4 m
CU-LPS5BL005M	Blue	5 m
CU-LPS5BL007M	Blue	7 m

CU-LPS5GY001M	Grey	1 m
CU-LPS5GY002M	Grey	2 m
CU-LPS5GY003M	Grey	3 m
CU-LPS5GY004M	Grey	4 m
CU-LPS5GY005M	Grey	5 m
CU-LPS5GY007M	Grey	7 m
CU-LPS5RD001M	Red	1 m
CU-LPS5RD002M	Red	2 m
CU-LPS5RD003M	Red	3 m
CU-LPS5RD004M	Red	4 m
CU-LPS5RD005M	Red	5 m
CU-LPS5RD007M	Red	7 m
CU-LPS5EW001M	White	1 m
CU-LPS5EW002M	White	2 m
CU-LPS5EW003M	White	3 m
CU-LPS5EW004M	White	4 m
CU-LPS5EW005M	White	5 m
CU-LPS5EW007M	White	7 m
CU-LPS5YL001M	Yellow	1 m
CU-LPS5YL002M	Yellow	2 m
CU-LPS5YL003M	Yellow	3 m
CU-LPS5YL004M	Yellow	4 m
CU-LPS5YL005M	Yellow	5 m
CU-LPS5YL007M	Yellow	7 m

History

Update and Revision:	Revision Number: 0.40 Revision Date: 11-21-2024
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.