



**Product:** [WireNet CAT5e Patch cord UTP](#)

WireNet CAT5e Patch cord UTP LSZH



## Product Description

WireNet CAT5e Unshielded LSZH Patch cord, 26AWG, Stranded

## Technical Specifications

### Product Overview

Suitable Applications:	Telecommunications Room, Main Distribution Room, Data Centers
------------------------	---------------------------------------------------------------

### Physical Characteristics (Overall)

Wiring Scheme:	T568A/B-T568A/B
Packaging:	Individually packaged in a sealed plastic bag.

### Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
----------------------	----------------------------------

### Temperature Range

Operating Temperature Range:	-20°C to +60°C
------------------------------	----------------

### Standards

Data Category:	Category 5e
TIA/EIA Compliance:	ISO/IEC 11801-1:2017; TIA 568-C.3

### Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

### Related Part Numbers

Related Parts:	WireNet Jacks (CU-J....) , WireNet Panel (NN-UNIV-E) or KeyConnect empty panels (AX....)
----------------	------------------------------------------------------------------------------------------

### Variants

Item #	Color	Length
CU-LPU5BK001M	Black	1 m
CU-LPU5BK002M	Black	2 m
CU-LPU5BK003M	Black	3 m
CU-LPU5BK004M	Black	4 m
CU-LPU5BK005M	Black	5 m
CU-LPU5BK007M	Black	7 m
CU-LPU5BL001M	Blue	1 m
CU-LPU5BL002M	Blue	2 m
CU-LPU5BL003M	Blue	3 m
CU-LPU5BL004M	Blue	4 m
CU-LPU5BL005M	Blue	5 m
CU-LPU5BL007M	Blue	7 m

CU-LPU5GY001M	Grey	1 m
CU-LPU5GY002M	Grey	2 m
CU-LPU5GY003M	Grey	3 m
CU-LPU5GY004M	Grey	4 m
CU-LPU5GY005M	Grey	5 m
CU-LPU5GY007M	Grey	7 m
CU-LPU5RD001M	Red	1 m
CU-LPU5RD002M	Red	2 m
CU-LPU5RD003M	Red	3 m
CU-LPU5RD004M	Red	4 m
CU-LPU5RD005M	Red	5 m
CU-LPU5RD007M	Red	7 m
CU-LPU5EW001M	White	1 m
CU-LPU5EW002M	White	2 m
CU-LPU5EW003M	White	3 m
CU-LPU5EW004M	White	4 m
CU-LPU5EW005M	White	5 m
CU-LPU5EW007M	White	7 m
CU-LPU5YL001M	Yellow	1 m
CU-LPU5YL002M	Yellow	2 m
CU-LPU5YL003M	Yellow	3 m
CU-LPU5YL004M	Yellow	4 m
CU-LPU5YL005M	Yellow	5 m
CU-LPU5YL007M	Yellow	7 m

## History

Update and Revision:	Revision Number: 0.40 Revision Date: 11-21-2024
----------------------	-------------------------------------------------

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.