



**Product:** [WireNet CAT6A Patch cord STP](#)

WireNet CAT6A Patch cord STP LSZH



## Product Description

WireNet CAT6A Shielded LSZH Patch cord, 26AWG, Stranded

## Technical Specifications

### Product Overview

Suitable Applications:	Telecommunications Room, Main Distribution Room, Data Centers
------------------------	---

### Physical Characteristics (Overall)

Wiring Scheme:	T568A/B-T568A/B
Packaging:	Individually packaged in a sealed plastic bag.

### Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
----------------------	----------------------------------

### Temperature Range

Operating Temperature Range:	-20°C to +60°C
------------------------------	----------------

### Standards

Data Category:	Category 6A
TIA/EIA Compliance:	ISO/IEC 11801-1:2017; TIA 568-C.3

### Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

### Flammability, LS0H, Toxicity Testing

IEC Flammability:	IEC 60332-3-22
-------------------	----------------

### Related Part Numbers

Related Parts:	WireNet Jacks (CU-J....) , WireNet Panel (NN-UNIV-E) or KeyConnect empty panels (AX....)
----------------	--

### Variants

Item #	Color	Length
CU-LPSABK001M	Black	1 m
CU-LPSABK002M	Black	2 m
CU-LPSABK003M	Black	3 m
CU-LPSABK004M	Black	4 m
CU-LPSABK005M	Black	5 m
CU-LPSABK007M	Black	7 m
CU-LPSABL001M	Blue	1 m
CU-LPSABL002M	Blue	2 m
CU-LPSABL003M	Blue	3 m

CU-LPSABL004M	Blue	4 m
CU-LPSABL005M	Blue	5 m
CU-LPSABL007M	Blue	7 m
CU-LPSAGY001M	Grey	1 m
CU-LPSAGY002M	Grey	2 m
CU-LPSAGY003M	Grey	3 m
CU-LPSAGY004M	Grey	4 m
CU-LPSAGY005M	Grey	5 m
CU-LPSAGY007M	Grey	7 m
CU-LPSARD001M	Red	1 m
CU-LPSARD002M	Red	2 m
CU-LPSARD003M	Red	3 m
CU-LPSARD004M	Red	4 m
CU-LPSARD005M	Red	5 m
CU-LPSARD007M	Red	7 m
CU-LPSAEW001M	White	1 m
CU-LPSAEW002M	White	2 m
CU-LPSAEW003M	White	3 m
CU-LPSAEW004M	White	4 m
CU-LPSAEW005M	White	5 m
CU-LPSAEW007M	White	7 m
CU-LPSAYL001M	Yellow	1 m
CU-LPSAYL002M	Yellow	2 m
CU-LPSAYL003M	Yellow	3 m
CU-LPSAYL004M	Yellow	4 m
CU-LPSAYL005M	Yellow	5 m
CU-LPSAYL007M	Yellow	7 m

## History

Update and Revision:	Revision Number: 0.44 Revision Date: 04-12-2024
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.