



For more Information
please call

1-800-Belden1



General Description:

16 AWG triads stranded (7x24) bare copper conductors, twisted triads, overall Beldfoil shield (100% coverage), PVC insulation, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	# Triads	AWG	Stranding	Conductor Material
1	16	16	7x24	BC - Bare Copper

Total Number of Conductors: 49

Insulation

Insulation Material:

Insulation Material
F-R PVC - Flame Retardant Polyvinyl Chloride

Communication Wire

Communication Wire AWG: 22

Communication Wire Material: BC - Bare Copper

Communication Wire Stranding: 7x30

Inner Shield

Inner Shield Color Code Chart:

Number	Color
1	Black & White & Red and numbered 1
2	Black & White & Red and numbered 2
3	Black & White & Red and numbered 3
4	Black & White & Red and numbered 4
5	Black & White & Red and numbered 5
6	Black & White & Red and numbered 6
7	Black & White & Red and numbered 7
8	Black & White & Red and numbered 8
9	Black & White & Red and numbered 9
10	Black & White & Red and numbered 10
11	Black & White & Red and numbered 11
12	Black & White & Red and numbered 12
13	Black & White & Red and numbered 13
14	Black & White & Red and numbered 14
15	Black & White & Red and numbered 15
16	Black & White & Red and numbered 16
17	Orange

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
18	7x26	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
F-R PVC - Flame Retardant Polyvinyl Chloride	1.8796

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 26.187 mm

Pair

Pair Lay Length & Direction:

Twists (twist/m)
6

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +105°C

Bulk Cable Weight: 1101.270 Kg/Km

Max. Recommended Pulling Tension: 7819.940 N

Min. Bend Radius/Minor Axis: 285.750 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: PLTC, ITC, CMG

CEC/C(UL) Specification: CMG

AWM Specification: UL Style 2464 (300 V 105°C)

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 FT4 Loading

CSA Flame Test: FT4

IEEE Flame Test: 1202

ICEA Flame Test: T-29-520

Suitability

Sunlight Resistance: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)
0.511836

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

177.502

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
12.1397

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
16.0769

Max. Operating Voltage - UL:

Voltage
300 V RMS

Notes (Overall)

Notes: Alternate color coding available upon request.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 1 Revision Date: 05-14-2007

© 2020 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.