



**Product:** [WireNet Shielded CAT5E Jack](#)



WN STP CAT5E Jack

**Product Description**

WireNet Shielded CAT5E Jack

**Technical Specifications**

**Physical Characteristics (Overall)**

Packaging:	Individually packaged in a sealed plastic bag.
------------	--

**Temperature Range**

Operating Temperature Range:	-20°C to +60°C
------------------------------	----------------

**Mechanical Characteristics**

Termination Front Connection:	Mated Connection
Termination Front Connection Durability:	750 cycles
Termination Rear Connection:	Mated Connection
Termination Rear Connection Durability:	20 cycles

**Standards**

Data Category:	Category 6
TIA/EIA Compliance:	ISO/IEC 11801-1:2017; TIA 568.2-D

**Applicable Environmental and Other Programs**

Environmental Space:	Indoor
EU Directive 2011/65/EU (RoHS 2):	Yes

**Related Part Numbers**

Related Parts:	WireNet Patch Cords (CU-LP....) , WireNet Panel (NN-UNIV-E) or KeyConnect empty panels (AX....)
----------------	---

**Variants**

Item #	Color	Packaging
CU-JS5ME	Metal	Individually packaged in a sealed plastic bag.

**Product Notes**

Notes:	Insulation O.D. Range = 0.90 to 1.6 mm, Cable Jacket O.D. Max = 9.2 mm
--------	--

**History**

Update and Revision:	Revision Number: 0.39 Revision Date: 09-25-2023
----------------------	---

at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.