


For more Information  
please call

1-800-Belden1



### General Description:

22 and 24 AWG stranded tinned copper conductors, PVC insulation (power), FPE insulation (Data), individually foil shielded (100% coverage) and an overall tinned copper braid (65% coverage), CPE jacket.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Conductors	# Pairs	AWG	Stranding	Conductor Material
4	1	22	19x34	TC - Tinned Copper
	1	24	19x36	TC - Tinned Copper

#### Insulation

##### Insulation Material:

Insulation Material	AWG
PVC - Polyvinyl Chloride	22
FPE - Foam Polyethylene	24

#### Inner Shield

##### Inner Shield Material:

Layer #	Type	Inner Shield Material	Coverage (%)
22 AWG Pair	Tape	Aluminum Foil-Polyester Tape	100
24 AWG Pair	Tape	Aluminum Foil-Polyester Tape	100

##### Inner Shield Drain Wire AWG:

AWG
22

Inner Shield Drain Wire Stranding: 19x34

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

#### Outer Shield

##### Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	65

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Material
CPE - Chlorinated Polyethylene

#### Overall Cable

Overall Nominal Diameter: 7.112 mm

#### Pair

##### Pair Color Code Chart:

Number	Color
22 AWG Pair	Red & Black
24 AWG Pair	Blue & White

### Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +75°C

## 3085A Multi-Conductor - DeviceBus® for ODVA DeviceNet™

UL Temperature Rating:	75°C
Bulk Cable Weight:	68.457 Kg/Km
Max. Recommended Pulling Tension:	289.133 N
Min. Bend Radius/Minor Axis:	69.850 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG, CL2
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/13/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	ODVA Class 2 Thin

#### Flame Test

UL Flame Test:	UL1685 FT4 Loading
CSA Flame Test:	FT4

#### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

### Electrical Characteristics (Overall)

#### Nom. Characteristic Impedance:

Description	Impedance (Ohm)
24 AWG Pair	120

#### Nom. Capacitance Conductor to Conductor:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Capacitance (pF/m)
24 AWG Pair	1			39.372

#### Nominal Velocity of Propagation:

Description	VP (%)
24 AWG Pair	75

#### Maximum Delay:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Delay (ns/m)
24 AWG Pair				4.46216

#### Maximum Conductor DC Resistance:

Description	DCR @ 20°C (Ohm/100 m)
22 AWG	57.4175
24 AWG	91.868

#### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
10.4992

#### Max. Attenuation:

()	Description	Freq. (MHz)
0.95149	24 AWG Pair Only	.125
1.6405		.500
2.2967		1.000

## 3085A Multi-Conductor - DeviceBus® for ODVA DeviceNet™

### Max. Operating Voltage - UL:

Voltage
300 V RMS

### Max. Recommended Current:

Current
1.7 Amps per conductor @ 25°C (24 AWG)
4 Amps per conductor @ 24 V per NEC CL2 (Power Pair)

### Notes (Overall)

**Notes:** Thin. Meter marks on jacket to aid users in installation. ODVA DeviceNet is an Open DeviceNet Vendor Association, Inc. trademark.

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
3085A 5601000	1,000 FT	47.000 LB	YELLOW, BRIGHT	C	2 #22, 2 #24 SHLD CPE
3085A 5602000	2,000 FT	96.000 LB	YELLOW, BRIGHT	C	2 #22, 2 #24 SHLD CPE
3085A 5605000	500 FT	23.500 LB	YELLOW, BRIGHT	C	2 #22, 2 #24 SHLD CPE
3085A 5605000	5,000 FT	235.000 LB	YELLOW, BRIGHT	C Z	2 #22, 2 #24 SHLD CPE

#### Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 1    Revision Date: 05-14-2007

© 2019 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.