



For more Information  
please call

1-800-Belden1



### General Description:

14 AWG solid bare copper-covered steel conductor, foam FEP insulation, Duobond® IV Quad Shield (100% coverage), fluorocopolymer Jacket.

### Usage (Overall)

Suitable Applications: Plenum RG-11/U Type

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	14	Solid	BCCS - Bare Copper Covered Steel	1.6256

Total Number of Conductors: 1

#### Insulation

Insulation Material:

Insulation Material	Dia. (mm)
FFEP - Foam Fluorinated Ethylene Propylene	7.112

#### Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	AL - Aluminum	60
3	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
4		Braid	AL - Aluminum	40

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVDF - Fluorocopolymer

#### Overall Cable

Overall Nominal Diameter: 9.830 mm

### Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +150°C

Non-UL Temperature Rating: 150°C

Bulk Cable Weight: 101.198 Kg/Km

Max. Recommended Pulling Tension: 1374.490 N

Min. Bend Radius/Minor Axis: 101.600 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP

CEC/C(UL) Specification: CMP

## 3095A Coax - ControlBus™ Quad Shielded Coax

EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	11/U

### Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

### Suitability

Suitability - Outdoor:	Yes
Suitability - Burial:	Yes

### Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	3094A

### Surface Printing (Overall)

Surface Printing:	CONTROLBUS(R) BY BELDEN - 3095A RG-11/U TYPE 150C QUAD SHIELD 1C14 E108998 (UL) CMP OR C(UL) CMP
-------------------	---

### Electrical Characteristics (Overall)

#### Nom. Characteristic Impedance:

Impedance (Ohm)	Tolerance (Ohms)
75	± 3

#### Nom. Inductance:

Inductance (µH/m)
0.318257

#### Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)
54.1365

#### Nominal Velocity of Propagation:

VP (%)
82

#### Nominal Delay:

Delay (ns/m)
3.9372

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
36.091

#### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
12.7959

#### Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1	0.55777
2	0.72182
5	0.91868

## METRIC MEASUREMENT VERSION

## 3095A Coax - ControlBus™ Quad Shielded Coax

10	1.3124
20	1.9686
50	3.9372
100	5.5777
200	8.2025
300	9.97424
400	11.4835

### Max. Operating Voltage - UL:

<b>Voltage</b>
300 V RMS

**Other Electrical Characteristic 1:** Tilt 5 to 10 MHz: .42 dB/100 M

**Other Electrical Characteristic 2:** Tilt 10 to 20 MHz: .58 dB/100 M

### Minimum Structural Return Loss:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
		5	400	20

### Phase Delay Distortion:

F/B	%PDD/100M (5MB)	%PDD/100M (10MB)
0.5	-0.60	-1.27
1.0	-0.46	-0.43
1.5	0	0
2.0	+0.17	+0.27
2.5	+0.30	+0.45

## Notes (Overall)

**Notes:** Sweep tested 5 to 400 MHz. Tap marks every 2.6 meters to aid users in installation.

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
3095A F2V1000	1,000 FT	76.000 LB	GRAY, DEC	C	#14 FFEP DBSH PVDF

**Notes:**  
C = CRATE REEL PUT-UP.

Revision Number: 1    Revision Date: 04-25-2008

© 2020 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.