



Product: [3105A](#)

RS-485, 1 Pr, 22AWG, Str TC, PE Ins, OS+TC Brd, PVC Jkt, CM, PLTC, Sun Res, Oil Resistant

[Request Sample](#)

Product Description

RS-485, 120 Ohm, 1 pair 22AWG (7x30) tinned copper Datalene® insulaton, Overall Foil + 65% Tinned Copper Braid, PVC jacket, CM, PLTC, SUN RES and oil-resistant

Technical Specifications

Product Overview

Suitable Applications:	harsh environment, IIoT, factory or process automation, video, audio, data communication, etc.
------------------------	--

Construction Details

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	22 AWG	7x30	TC - Tinned Copper

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code	Notes
Pair(s)	PE - Polyethylene (Foam)	0.029 in (0.74 mm)	0.087 in (2.2 mm)	White/Blue Stripe & Blue/White Stripe	HDPE

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC
Braid	Tinned Copper (TC)	65%	

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.047 in (1.2 mm)	0.294 in (7.47 mm)

Table Notes:	Jacket OD +/- 0.006
Overall Cable Diameter (Nominal):	0.294 in (7.47 mm)

Electrical Characteristics

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Pair(s)	18.2 Ohm/1000ft	11 pF/ft (36 pF/m)	20.9 pF/ft	120 Ohm	78%	6 Amps per Conductor at 30°C
Conductor(s)						
Nom. Outer Shield DCR:		4.685 Ohm/1000ft (15.37 Ohm/km)				

High Frequency (Nominal/Typical)

Element	Frequency [MHz]	Nom. Insertion Loss (Attenuation)
Pair(s)	1	0.5 dB/100ft

Voltage

UL Voltage Rating
300 V (CM, PLTC)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-20°C to +60°C

Bend Radius

Stationary Min.	Installation Min.
3.372 in (85.65 mm)	3.372 in (85.65 mm)

Max. Pull Tension:	53.34 lbs (24.19 kg)
Bulk Cable Weight:	43 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Oil Resistance
Flammability / Reaction to Fire:	UL 1685 UL Loading, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 725, Article 800, CM, PLTC
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Oil Resistance: Passes Oil Res II Per UL1277, Table 10.17. For CPE jacketed version order Part No. YR44345.
--------	---

History

Update and Revision:	Revision Number: 0.596 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
3105A 01010000	Black			612825386551	
3105A.00152	Black	Reel	152 m	8719605005816	
3105A.00305	Black	Reel	305 m	8719605005830	
3105A 010500	Black	Reel	500 ft	612825141600	C
3105A.00610	Black	Reel	610 m	8719605005854	
3105A 0101000	Black	Reel	1,000 ft	612825141594	C
3105A.001000	Black	Reel	1,000 m	8719605005809	
3105A.001525	Black	Reel	1,525 m	8719605005823	
3105A.003050	Black	Reel	3,050 m	8719605005847	
3105A 0105000	Black	Reel	5,000 ft	612825141617	C N

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.