



For more Information
please call

1-800-Belden1



General Description:

18 AWG solid bare copper-covered steel conductor, plenum, foam FEP insulation, Duobond® IV quad shield (100% coverage), fluorocopolymer jacket.

Usage (Overall)

Suitable Applications: Plenum RG-6/U Type

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	18	Solid	BCCS - Bare Copper Covered Steel	1.016

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
FFEP - Foam Fluorinated Ethylene Propylene	4.318

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	AL - Aluminum	60
3	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
4		Braid	AL - Aluminum	40

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVDF - Fluorocopolymer

Overall Cable

Overall Nominal Diameter: 6.960 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +150°C

UL Temperature Rating: 150°C

Bulk Cable Weight: 63.993 Kg/Km

Max. Recommended Pulling Tension: 462.613 N

Min. Bend Radius/Minor Axis: 69.850 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP

CEC/C(UL) Specification: CMP

3132A Coax - ControlBus™ Quad Shielded Coax

EU Directive 2011/65/EU (ROHS II):	Yes
IEEE Specification:	802.4 MAP, 802.7 Mini-MAP
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	6/U

Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

Suitability

Suitability - Outdoor:	Yes
Suitability - Burial:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	3131A

Surface Printing (Overall)

Surface Printing:	CONTROLBUS(R) BY BELDEN - 3132A RG-6/U TYPE 150C QUAD SHIELD 1C18 E108998 (UL) CMP OR C(UL) CMP
-------------------	--

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)	Tolerance (Ohms)
75	± 3

Nom. Inductance:

Inductance (µH/m)
0.305133

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)
53.4803

Nominal Velocity of Propagation:

VP (%)
82

Nominal Delay:

Delay (ns/m)
3.9372

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
91.868

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
23.6232

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100m)

1	1.18116
2	1.24678
5	1.6405
10	2.13265
20	3.11695
50	4.9215
100	6.95572
200	9.81019
300	12.0085
400	13.8786

Max. Operating Voltage - UL:

Voltage
300 V RMS

Other Electrical Characteristic 1: Tilt 5 to 10 MHz: .48 dB/100 M

Other Electrical Characteristic 2: Tilt 10 to 20 MHz: .93 dB/100 M

Other Electrical Characteristic 3: Sweep Tested 5 to 400MHz.

Minimum Structural Return Loss:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
		5	400	23

Phase Delay Distortion:

F/B	%PDD/100M (5MB)	%PDD/100M (10MB)
0.5	-0.54	-1.19
1.0	-0.19	-0.51
1.5	0	0
2.0	+0.16	+0.38
2.5	+0.30	+0.66

Notes (Overall)

Notes: Tap Marks Every 2.6 Meters to aid in users installation.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
3132A F2V1000	1,000 FT	36.000 LB	GRAY, DEC	C	#18 FFEP DBSH SLF

Notes:
C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-25-2008

© 2020 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).