



For more Information
please call

1-800-Belden1



General Description:

The glass braid offers abrasion resistance, is treated to prevent fraying. The Silicone insulation strips easy and clean. Recommended for high-temperature applications in motors, lighting fixtures, clothes dryers, stoves, therapeutic and electronic devices

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	14	7x22	TC - Tinned Copper

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
Silicone with Lacquered Glass Braid Covering	0.762

Overall Insulation

Overall Cable

Overall Nominal Diameter: 4.242 mm

Mechanical Characteristics (Overall)

UL Temperature Rating: 200°C (UL AWM Style 3071)

Bulk Cable Weight: 35.717 Kg/Km

Recommended Maximum Baking Cycles: 24 hours @ 410°F (210°C)

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL AWM Style: UL Style 3071 (600 V 200°C)

UL Rating: 600 V, 200°C, VW-1

CSA Rating: 600 V, 200°C

CSA Type: SEW-2

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Plenum/Non-Plenum

Plenum (Y/N):

No

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
32414 0094000	4,000 FT	100.000 LB	WHITE	C I	#14 SIL GL BRD 200C 600V
32414 009500	500 FT	13.000 LB	WHITE	F	#14 SIL GL BRD 200C 600V
32414 0104000	4,000 FT	100.000 LB	BLACK	C I	#14 SIL GL BRD 200C 600V
32414 010500	500 FT	13.000 LB	BLACK	F	#14 SIL GL BRD 200C 600V

Notes:

C = CRATE REEL PUT-UP.

F = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'

I = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 200'

Revision Number: 1 Revision Date: 07-17-2012

© 2020 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).