

For more Information
please call

1-800-Belden1



General Description:

The 333 series of braidless Silicone 150°C lead wire features easy and clean stripping without the problems associated with glass braid wire. It has excellent physical and mechanical strength properties.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	6	84x25	TC - Tinned Copper

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
Silicone Rubber	1.524

Separator

Separator Material over Conductor: Y

Overall Insulation

Overall Cable

Overall Nominal Diameter: 8.484 mm

Mechanical Characteristics (Overall)

Non-UL Temperature Rating: 150°C

Bulk Cable Weight: 101.198 Kg/Km

Recommended Maximum Baking Cycles: 24 hours @ 410°F (210°C)

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL AWM Style:	3213
UL Rating:	600 V, 150°C
CSA Rating:	600 V, 150°C
CSA Type:	AWM
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
33306 010500	500 FT	61.500 LB	BLACK	C F	#6 STR SIL 150C 600V

Notes:

C = CRATE REEL PUT-UP.

F = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'

Revision Number: 1 Revision Date: 05-14-2007

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.