


1072A Multi-Conductor - 600V Tray Cable

For more Information
please call

1-800-Belden1



General Description:

16 AWG pairs stranded (7x24) bare copper conductors, twisted pairs, PVC/Nylon insulation, overall Beldfoil shield (100% coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
12	16	7x24	BC - Bare Copper

Total Number of Conductors: 24

Insulation

Insulation Material:

Insulation Material
PVC/Nylon - Polyvinyl Chloride/Nylon

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
16	7x24	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.6002

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Lay Length & Direction:

Length (mm)
231.393089

Overall Nominal Diameter: 20.625 mm

Pair

Pair Color Code Chart:

Number	Color
1	Black & White and Numbered 1
2	Black & White and Numbered 2
3	Black & White and Numbered 3
4	Black & White and Numbered 4
5	Black & White and Numbered 5
6	Black & White and Numbered 6
7	Black & White and Numbered 7
8	Black & White and Numbered 8
9	Black & White and Numbered 9
10	Black & White and Numbered 10

11	Black & White and Numbered 11
12	Black & White and Numbered 12

Pair Lay Length & Direction:

Lay Length (mm)
63.49975
69.849725

Mechanical Characteristics (Overall)

Wet Temperature Range:	-30°C To +75°C
Dry Temperature Range:	-30°C To +90°C
Bulk Cable Weight:	551.527 Kg/Km
Max. Recommended Pulling Tension:	3972.240 N
Min. Bend Radius/Minor Axis:	205.740 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	NPLF, TC-ER
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	ICEA S-73-532, S-61-402

Flame Test

UL Flame Test:	UL1685 UL Loading
C(UL) Flame Test:	FT4
IEEE Flame Test:	1202

Suitability

Suitability - Burial:	Yes
Sunlight Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
----------------------	----

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
12.0413

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
9.48209

Max. Operating Voltage - UL:

Voltage
600 V RMS (NEC Type TC)
150 V RMS (NPLF)

Notes (Overall)

Notes: Alternate color coding available upon request.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1072A 0105000	5,000 FT	2,200.000 LB	BLACK	C Z	12 PR #16 PVC/NYL FS PVC

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 1 Revision Date: 02-13-2014

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.