Detailed Specifications & Technical Data

METRIC MEASUREMENT VERSION



5000UH Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled



For more Information please call

1-800-Belden1



General Description:

Security & Commercial Audio Cable, Riser-CL3R-FPLR 2-12 AWG stranded tinned copper conductors with polyolefin insulation, PVC jacket with ripcord

Usage (Overall)

Suitable Applications: Intercom/PA Systems, Sound/Audio Systems, Fire Alarm (For color Red

only)(Dual Rated)

2

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	12	19x25	TC - Tinned Copper

Total Number of Conductors:

Insulation

Insulation Material:

| Insulation Material | Wall Thickness (mm) | PP - Polypropylene | 0.279 |

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)			
PVC - Polyvinyl Chloride	0.432			

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Color Code Chart:

Number	Color		
1	Black		
2	White		

Overall Nominal Diameter: 6.604 mm

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +75°C
Bulk Cable Weight:	74.410 Kg/Km
Max. Recommended Pulling Tension:	676.126 N
Min. Bend Radius/Minor Axis:	69.850 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CL3R, FPLR

Page 1 of 3 11-03-2020

Detailed Specifications & Technical Data





5000UH Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled

NEC Articles:	725 or 760
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Flame Test	
UL Flame Test:	UL1666 Vertical Riser
CSA Flame Test:	FT4
Suitability	
Suitability - Indoor:	Yes
Plenum/Non-Plenum	
Plenum (Y/N):	No
Plenum Number:	6000UH

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m) 0.49215

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m) 78.744

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km) 5.2496

Max. Operating Voltage - UL:

Voltage 300 V RMS

Max. Recommended Current:

Description		Current		
	10C Temperature Rise	12 Amps per conductor @ 25°C ambient		

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5000UH 0081000	1,000 FT	54.000 LB	GRAY		2 #12 PO FRPVC
5000UH 008500	500 FT	29.000 LB	GRAY		2 #12 PO FRPVC
5000UH 0101000	1,000 FT	54.000 LB	BLACK		2 #12 PO FRPVC

Revision Number: 0 Revision Date: 08-28-2015

© 2020 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

Page 2 of 3 11-03-2020

Detailed Specifications & Technical Data

METRIC MEASUREMENT VERSION



5000UH Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled

All sales of Belden products are subject to Belden's standard terms and conditions of sale.
Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Page 3 of 3 11-03-2020