

1229A1 Multi-Conductor - Category 3 Nonbonded-Pair Cable



For more Information
please call

1-800-Belden1



General Description:

CAT3, 4-Pair, U/UTP-Unshielded, Riser-CMR, Premise Horizontal Cable, 24 AWG Solid Bare Copper Conductors, Polyolefin Insulation, PVC Jacket

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	24	Solid	BC - Bare Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material
PO - Polyolefin

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (mm)
5.004

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +75°C
Bulk Cable Weight:	43.158 Kg/Km
Max. Recommended Pulling Tension:	155.687 N
Min. Bend Radius/Minor Axis:	25.400 mm
Min. Bend/Installation:	48.260 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR, CMX-Outdoor

1229A1 Multi-Conductor - Category 3 Nonbonded-Pair Cable

CEC/C(UL) Specification:	CMR, CMX-Outdoor
EU Directive 2011/65/EU (ROHS II):	Yes
IEEE Specification:	802.3 10BaseT, 100BaseT4
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	NEMA WC-63 Category 3, Verified to ANSI/TIA-586-C.2, Category 3

Flame Test

UL Flame Test:	UL1666 Vertical Riser
C(UL) Flame Test:	FT4
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	1245A2

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/m)

49.215

Maximum Capacitance Unbalance (pF/100 m): 330

Nominal Velocity of Propagation:

VP (%)

70

Maximum Delay:

Delay (ns/100 m)

538 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m)

45

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)

9.38

Max. Operating Voltage - UL:

Voltage

300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

5

Electrical Characteristics-Premise (Overall)

Premise Cable Electricals:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. SRL (dB)	Fitted Imp. (Ohms)
1	2.56	41.0	No Spec	12.0	100 ± 15%

1229A1 Multi-Conductor - Category 3 Nonbonded-Pair Cable

4	5.58	32.0	No Spec	12.0	100 ± 15%
10	9.71	26.0	No Spec	12.0	100 ± 15%
16	13.10	23.0	No Spec	9.96	100 ± 15%

Notes (Overall)

Notes: Jacket sequentially marked at 2 ft. intervals. Third party verified to ANSI/TIA-568-C.2, Category 3.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1229A1 008U1000	1,000 FT	22.000 LB	GRAY		CAT3 4PR U/UTP CMR BOX

Revision Number: 4 Revision Date: 02-06-2013

© 2019 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).