

For more Information  
please call

1-800-Belden1



### General Description:

Security & Alarm Cable, Rated-CMG-FPL-PLTC-ER, 1-18 AWG stranded tinned copper pair with PVC insulation, Beldfoil® shield, Waterblocking tape, PVC jacket

### Usage (Overall)

**Suitable Applications:** Low Voltage, Water-Blocked for Use in Underground Ducts, PLTC, FPL, Intercom, Sound, Audio

### Physical Characteristics (Overall)

#### Conductor

**AWG:**

# Pairs	AWG	Stranding	Conductor Material
1	18	7x26	TC - Tinned Copper

**Total Number of Conductors:** 2

#### Insulation

**Insulation Material:**

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.254

#### Outer Shield

**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

**Outer Shield Drain Wire AWG:**

AWG	Stranding	Drain Wire Conductor Material
24	solid	TC - Tinned Copper

**Outer Shield Waterblocking Tape:** Yes

#### Outer Jacket

**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.9398

#### Overall Cable

**Overall Nominal Diameter:** 5.893 mm

#### Pair

**Pair Color Code Chart:**

Number	Color
1	Black & Red

### Mechanical Characteristics (Overall)

**Operating Temperature Range:** -30°C To +105°C

**UL Temperature Rating:** 105°C

**Bulk Cable Weight:** 40.181 Kg/Km

**Max. Recommended Pulling Tension:** 253.547 N

Min. Bend Radius/Minor Axis: 63.500 mm

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG, FPL, PLTC
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	11/08/2006
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	PLTC-ER

### Flame Test

UL Flame Test:	UL1685 FT4/IEEE 1202 Vertical Tray Flame Test
C(UL) Flame Test:	FT4
Other Flame Test:	IEEE 1202

### Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Burial:	Yes - UL
Sunlight Resistance:	Yes

### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Electrical Characteristics (Overall)

### Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)  
213.265

### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)  
19.3579

### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)  
55.449

### Max. Operating Voltage - UL:

Voltage  
300 V RMS

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5340F1 0021000	1,000 FT	30.000 LB	RED	C	1 FS PR #18 PVC PVC
5340F1 010Z1000	1,000 FT	33.000 LB	BLACK		1 FS PR #18 PVC PVC
5340F1 0101000	1,000 FT	30.000 LB	BLACK	C	1 FS PR #18 PVC PVC
5340F1 0105000	5,000 FT	140.000 LB	BLACK		1 FS PR #18 PVC PVC

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 4    Revision Date: 02-17-2016

© 2019 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).