



For more Information
please call

1-800-Belden1



General Description:

25 AWG solid .018" tinned copper conductor, gas-injected foam HDPE insulation, lightly bonded aluminum foil-polyester tape-aluminum foil shield with a 95% tinned copper braid shield, PVC jacket.

Usage (Overall)

Suitable Applications:

Analog video, digital video, Mini Hi-Res, video, VGA, SVGA, 825, RGB, Composite Video, Component Video, Video Distribution, Graphic Displays, special effects editing, animation, post production. Home Theater, boardrooms, office, casino, church, synagogue, house of worship, teleconferencing, digital

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	25.0	Solid	TC - Tinned Copper	0.4572

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FHDPE - Foam High Density Polyethylene	1.8796

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Light Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 2.896 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 60°C

Non-UL Temperature Rating: 75°C

Bulk Cable Weight: 11.906 Kg/Km

Max. Recommended Pulling Tension: 102.309 N

Min. Bend Radius/Minor Axis: 38.100 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR

CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	06/25/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1666 Vertical Riser
----------------	-----------------------

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	No
Suitability - Aerial:	No

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (µH/m)

0.347786

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

55.777

Nominal Velocity of Propagation:

VP (%)

80

Nominal Delay:

Delay (ns/m)

4.06844

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

111.554

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

17.7174

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100m)

1	1.70612
5	3.83877
50	12.1397
100	16.0769
200	21.9827
400	31.1695
700	43.9654
900	49.215

1000	51.8398
3000	102.367

Max. Operating Voltage - UL:

Voltage
300 V RMS

Other Electrical Characteristic 1: Impedance tested in accordance with ASTM D-4566 paragraph 48.2, option 2 using a 75 Ohm fixed bridge and termination. 75 +/- 3 Ohms

Other Electrical Characteristic 2: Return Loss tested in accordance with ASTM D-4566 paragraph 50.3, using a 75 Ohm fixed bridge and termination.

Minimum Return Loss:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
		5	850	20

Sweep Test

Sweep Testing: 100%; Sweep tested 5 MHz to 850 MHz.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1281R 0101000	1,000 FT	10.000 LB	BLACK	C	#25LDPE/GIFHDLDPE SH FRPVC

Notes:
C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 02-11-2013

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.