

1313A Multi-Conductor - Speaker Cable

For more Information
please call

1-800-Belden1



General Description:

10 AWG stranded (259x34) oxygen-free high-conductivity bare copper conductors, PO insulation, conductors cabled, PVC jacket. Sequential footage marking every two feet.

Usage (Overall)

Suitable Applications: Speaker Cable, Indoor/Outdoor Home Theater, In-Wall Speaker, Outdoor Speaker

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (mm)
2	10	259x34	High Conductivity BC - Bare Copper	3.3528

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
PO - Polyolefin	4.318

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red

Overall Nominal Diameter: 10.871 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 148.820 Kg/Km

Max. Recommended Pulling Tension: 1223.255 N

Min. Bend Radius/Minor Axis: 114.300 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CL3, CM

CEC/C(UL) Specification:	CM
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/11/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	Sunlight resistant in Black and White.

Flame Test

UL Flame Test:	UL1581 Vertical Flame and FT-1 Flame Test
CSA Flame Test:	FT1

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6T00UP

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)
0.49215

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
76.1192

Nominal Velocity of Propagation:

VP (%)
66

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
3.281

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
17 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1313A 0081000	1,000 FT	109.000 LB	GRAY	C	2 #10 PE FRPVC
1313A 008500	500 FT	55.000 LB	GRAY	C	2 #10 PE FRPVC
1313A 0101000	1,000 FT	109.000 LB	BLACK	C	2 #10 PE FRPVC
1313A 010500	500 FT	55.000 LB	BLACK	C	2 #10 PE FRPVC
1313A 1SL1000	1,000 FT	109.000 LB	WHITE 1SL	C	2 #10 PE FRPVC
1313A 1SL500	500 FT	55.000 LB	WHITE 1SL	C	2 #10 PE FRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 09-20-2017

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.