



For more Information  
please call

1-800-Belden1



### General Description:

Security & Alarm Cable, Riser-CMR, 2-22 AWG stranded bare copper pairs with polyolefin insulation, PVC jacket with ripcord

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
2	22	7x30	BC - Bare Copper

Total Number of Conductors: 4

#### Insulation

Insulation Material:

Insulation Material
PO - Polyolefin

#### Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.432

Outer Jacket Ripcord: Yes

#### Overall Cable

Overall Nominal Diameter: 4.699 mm

#### Pair

Pair Color Code Chart:

Number	Color
1	Black & Red
2	Black & White

### Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

Bulk Cable Weight: 22.323 Kg/Km

Max. Recommended Pulling Tension: 161.914 N

Min. Bend Radius/Minor Axis: 46.990 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR

CEC/C(UL) Specification: CMG

EU Directive 2011/65/EU (ROHS II): Yes

## 5541UE Multi-Conductor - Commercial Applications

EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

### Flame Test

CSA Flame Test:	FT4
-----------------	-----

### Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6541UE

## Electrical Characteristics (Overall)

### Nom. Capacitance Conductor to Conductor:

#### Capacitance (pF/m)

59.058

### Nom. Conductor DC Resistance:

#### DCR @ 20°C (Ohm/km)

53.4803

### Max. Operating Voltage - UL:

#### Voltage

300 V RMS

### Max. Recommended Current:

#### Current

2.2 Amps per conductor @ 20°C

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5541UE 008U1000	1,000 FT	17.000 LB	GRAY		2 PR #22 PP FRPVC
5541UE 008Z1000	1,000 FT	19.000 LB	GRAY		2 PR #22 PP FRPVC
5541UE 0081000	1,000 FT	17.000 LB	GRAY	C	2 PR #22 PP FRPVC

### Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2    Revision Date: 03-11-2013

© 2019 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

METRIC MEASUREMENT VERSION

## 5541UE Multi-Conductor - Commercial Applications

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).