

## 1468A Multi-Conductor - 300V Power-Limited Tray Cable



For more Information  
please call

1-800-Belden1



### General Description:

18 AWG pairs stranded (7x26) bare copper conductors, twisted pairs, PVC insulation, overall Beldfoil® shield (100% coverage), PVC jacket.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Conductors	# Pairs	AWG	Stranding	Conductor Material
	12	18	7x26	BC - Bare Copper
1		22	7x30	BC - Bare Copper

Total Number of Conductors: 25

#### Insulation

##### Insulation Material:

Insulation Material
PVC - Polyvinyl Chloride

#### Outer Shield

##### Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

##### Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
18	7x26		TC - Tinned Copper

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.600

Outer Jacket Ripcord: Yes

#### Overall Cable

Overall Nominal Diameter: 17.323 mm

#### Pair

##### Pair Color Code Chart:

Number	Color
1	Black & White and Numbered 1
2	Black & White and Numbered 2
3	Black & White and Numbered 3
4	Black & White and Numbered 4
5	Black & White and Numbered 5
6	Black & White and Numbered 6
7	Black & White and Numbered 7
8	Black & White and Numbered 8
9	Black & White and Numbered 9
10	Black & White and Numbered 10
11	Black & White and Numbered 11
12	Black & White and Numbered 12
Communication	Orange

### Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +105°C
Bulk Cable Weight:	384.849 Kg/Km
Max. Recommended Pulling Tension:	2490.992 N
Min. Bend Radius/Minor Axis:	170.180 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG, ITC-ER, PLTC-ER
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Flame Test

UL Flame Test:	UL1685 FT4 Loading
CSA Flame Test:	FT4
IEEE Flame Test:	1202

#### Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Burial:	Yes
Sunlight Resistance:	Yes

#### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

### Surface Printing (Overall)

Surface Printing:	BELDEN 1468A E34972 12PR18 1C22 SHIELDED (UL) CMG 105C OR PLTC OR ITC SUN RES DIR BUR OR AWM 2464 80C 300V OR C(UL) CMG----FT4 IEEE 1202 (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FEET
-------------------	---

### Electrical Characteristics (Overall)

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)	19.2267
---------------------	---------

#### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)	13.8458
---------------------	---------

#### Max. Operating Voltage - UL:

Voltage	300 V RMS
---------	-----------

## 1468A Multi-Conductor - 300V Power-Limited Tray Cable

### Notes (Overall)

**Notes:** Alternate color coding available upon request.

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1468A 0105000	5,000 FT	1,485.000 LB	BLACK	C Z	12 PR #18 + 1 #22 PVC FS PVC

**Notes:**

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 2    Revision Date: 05-17-2015

© 2020 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).