

1583A Multi-Conductor - Category 5e Nonbonded-Pair Cable



For more Information
please call

1-800-Belden1



General Description:

CAT5e (100MHz), 4-Pair, U/UTP-Unshielded, Riser-CMR, Premise Horizontal Cable, 24 AWG Solid Bare Copper Conductors, Polyolefin Insulation, Ripcord, PVC Jacket.

Usage (Overall)

Suitable Applications: Horizontal, 1000BaseT, Gigabit Ethernet, POE, POE+, 100BaseTX, Fast Ethernet, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Video, RS-422

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	24	Solid	BC - Bare Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material
PO - Polyolefin

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (mm)
4.826

Outer Jacket Ripcord: Yes

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Storage Temperature Range: -20°C To +75°C

Installation Temperature Range: 0°C To +60°C

Operating Temperature Range: -20°C To +60°C

1583A Multi-Conductor - Category 5e Nonbonded-Pair Cable

Bulk Cable Weight:	26.788 Kg/Km
Max. Recommended Pulling Tension:	155.687 N
Min. Bend Radius/Minor Axis:	20.320 mm
Min. Bend/Installation:	48.260 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR
NEC Articles:	800
CEC/C(UL) Specification:	CMR
EU Directive 2011/65/EU (ROHS II):	Yes
Other Standards:	ISO/IEC 11801 ed 2.1 (2008) Class D
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	Category 5e - TIA 568.C.2
Other Specification:	NEMA WC-63.1 Category 5e

Applicable Patents:

Country
www.belden.com/p

Flame Test

UL Flame Test:	UL1666 Vertical Riser
C(UL) Flame Test:	FT4
CSA Flame Test:	FT4
IEEE Flame Test:	1202

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	No
Suitability - Aerial:	No
Suitability - Burial:	No
Sunlight Resistance:	No
Oil Resistance:	No
Non-halogenated:	No

Plenum/Non-Plenum

Plenum (Y/N):	No
----------------------	----

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/m)
49.215

1583A Multi-Conductor - Category 5e Nonbonded-Pair Cable

Maximum Capacitance Unbalance (pF/100 m): 330

Nominal Velocity of Propagation:

VP (%)
70

Maximum Delay:

Delay (ns/100 m)
538 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m)
45

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
9.38

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)
3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)
1	2.000	65.3	62.3	63.0	60.3	20.000
4	4.100	56.3	53.3	51.0	49.2	23.000
8	5.800	51.8	48.8	46.0	43.0	24.500
10	6.500	50.3	47.3	43.0	40.8	25.000
16	8.200	47.3	44.3	39.0	36.0	25.000
20	9.300	45.8	42.8	36.5	33.5	25.000
25	10.400	44.3	41.3	33.9	30.9	24.300
31.25	11.700	42.9	39.9	31.0	28.2	23.600
62.5	17.000	38.4	35.4	22.0	19.0	21.500
100	22.000	35.3	32.3	14.0	10.3	20.100
155	28.100	32.5	29.5	4.4	1.4	15.800
200	32.400	30.8	27.8	4.0	1.0	15.000

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	63.8	60.8
4	100 ± 15	51.7	48.7
8	100 ± 15	45.7	42.7
10	100 ± 15	43.8	40.8
16	100 ± 15	39.7	36.7
20	100 ± 15	37.7	34.7
25	100 ± 15	35.8	32.8
31.25	100 ± 15	33.9	30.9
62.5	100 ± 15	27.8	24.9
100	100 ± 15	23.8	20.8
155	100 ± 25	19.9	16.9
200	100 ± 25	17.7	14.7

Notes (Overall)

Notes: Jacket sequentially marked at 2 ft. intervals. Third party verified to ANSI/TIA-568-C.2, Category 5e. Values above 100 MHz are for engineering purposes only.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

1583A Multi-Conductor - Category 5e Nonbonded-Pair Cable

1583A 002U1000	1,000 FT	24.000 LB	RED		CAT5E 4PR U/UTP CMR BOX
1583A 0021000	1,000 FT	5.000 LB	RED	C	CAT5E 4PR U/UTP CMR REEL
1583A 003U1000	1,000 FT	24.000 LB	ORANGE		CAT5E 4PR U/UTP CMR BOX
1583A 0031000	1,000 FT	20.000 LB	ORANGE	C	CAT5E 4PR U/UTP CMR REEL
1583A 004U1000	1,000 FT	24.000 LB	YELLOW		CAT5E 4PR U/UTP CMR BOX
1583A 0041000	1,000 FT	20.000 LB	YELLOW	C	CAT5E 4PR U/UTP CMR REEL
1583A 005U1000	1,000 FT	24.000 LB	GREEN, DARK		CAT5E 4PR U/UTP CMR BOX
1583A 0051000	1,000 FT	20.000 LB	GREEN, DARK	C	CAT5E 4PR U/UTP CMR REEL
1583A 006U1000	1,000 FT	20.000 LB	BLUE, LIGHT		CAT5E 4PR U/UTP CMR BOX
1583A 006Z1000	1,000 FT	22.000 LB	BLUE, LIGHT		CAT5E 4PR U/UTP CMR
1583A 0061000	1,000 FT	20.000 LB	BLUE, LIGHT	C	CAT5E 4PR U/UTP CMR REEL
1583A 0061640	1,640 FT	34.440 LB	BLUE, LIGHT		CAT5E 4PR U/UTP CMR REEL
1583A 0063000	3,000 FT	60.000 LB	BLUE, LIGHT		CAT5E 4PR U/UTP CMR REEL
1583A 008U1000	1,000 FT	20.000 LB	GRAY	C	CAT5E 4PR U/UTP CMR BOX
1583A 0081000	1,000 FT	20.000 LB	GRAY	C	CAT5E 4PR U/UTP CMR REEL
1583A 0081640	1,640 FT	34.440 LB	GRAY	C	CAT5E 4PR U/UTP CMR REEL
1583A 0083000	3,000 FT	60.000 LB	GRAY	C	CAT5E 4PR U/UTP CMR REEL
1583A 009U1000	1,000 FT	24.000 LB	WHITE		CAT5E 4PR U/UTP CMR BOX
1583A 0091000	1,000 FT	20.000 LB	WHITE	C	CAT5E 4PR U/UTP CMR REEL
1583A 0093000	3,000 FT	60.000 LB	WHITE	C	CAT5E 4PR U/UTP CMR REEL
1583A 010U1000	1,000 FT	24.000 LB	BLACK		CAT5E 4PR U/UTP CMR BOX
1583A 010Z1000	1,000 FT	22.000 LB	BLACK		CAT5E 4PR U/UTP CMR
1583A 0101000	1,000 FT	20.000 LB	BLACK	C	CAT5E 4PR U/UTP CMR REEL
1583A 012U1000	1,000 FT	24.000 LB	PINK		CAT5E 4PR U/UTP CMR BOX
1583A 0121000	1,000 FT	20.000 LB	PINK	C	CAT5E 4PR U/UTP CMR REEL

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 7 Revision Date: 09-18-2017

© 2020 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).