

METRIC MEASUREMENT VERSION

73403W Multi-Conductor - 600V Unshielded, Light to Moderate Flexing Applications Up to 1 Million Flex Life Cycles



For more Information
please call

1-800-Belden1

General Description:

14 AWG stranded (41x30) bare copper conductors, PVC insulation, oil-resistant PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	14	41x30	BC - Bare Copper

Total Number of Conductors: 3

Ground Wire

Ground Wire (Y/N): Y

Ground Wire AWG: 14

Ground Wire Stranding: 41x30

Ground Wire Conductor Material: BC - Bare Copper

Ground Wire Insulation Material: PVC - Polyvinyl Chloride

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.559

Insulation Color Code Chart:

Color	Description
Black	Individually Numbered
Yellow/Green	Ground

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.143

Overall Cable

Overall Nominal Diameter: 8.915 mm

Mechanical Characteristics (Overall)

Storage Temperature Range: -40°C To +90°C

Installation Temperature Range: Flexing: -5°C To +90°C

Bulk Cable Weight: 223.230 Kg/Km

Max. Recommended Pulling Tension: 431.475 N

Min. Bend Radius/Minor Axis: 45.720 mm

Min. Bend/Installation: 45.720 mm

Min. Bend Radius (Continuous Flexing): 45.720 mm

Flex Cycle Rating: 1 Million Flexes

METRIC MEASUREMENT VERSION

73403W Multi-Conductor - 600V Unshielded, Light to Moderate Flexing Applications Up to 1 Million Flex Life Cycles

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

AWM Specification:	UL Style 2587 (600 V 90°C)
CSA Specification:	600 V AWM I/II A/B
EU Directive 2011/65/EU (ROHS II):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	VDE 0472, Section 803 Oil Test, EU Low Voltage Directive 2014/35/EC, EU Directive 2011/65/EU(RoHS2), REACH Regulation (EC 1907/2006), California Proposition 65

Flame Test

CSA Flame Test:	FT1
------------------------	-----

Suitability

Suitability - Burial:	Yes
------------------------------	-----

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)
0.558

Max. Capacitance Conductor to Conductor:

Freq. (MHz)	Capacitance (pF/m)
0.001	118.116

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
8.531

Max. Operating Voltage - UL:

Voltage
600V

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
73403W 008100	100 FT	18.500 LB	GRAY		14AWG 41/30 3C UNSHIELDED
73403W 0081000	1,000 FT	155.000 LB	GRAY		14AWG 41/30 3C UNSHIELDED
73403W 008500	500 FT	80.000 LB	GRAY		14AWG 41/30 3C UNSHIELDED

Revision Number: 0 Revision Date: 09-27-2017

© 2020 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.