

For more Information
please call

1-800-Belden1



General Description:

Series 6, 18 AWG solid .040" bare copper-covered steel conductor, gas-injected foam polyethylene insulation, Duobond® II + AL braid shield (60% coverage), .045" bare copper-covered steel static ground, PVC jacket

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	18	Solid	BCCS - Bare Copper Covered Steel	1.016

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FPE - Foam Polyethylene	4.572

Static Ground

Static Ground: BCCS - Bare Copper Covered Steel

Static Ground Diameter: 1.143 mm

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	AL - Aluminum	60

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 6.858 x 10.287 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +80°C

Non-UL Temperature Rating: 80°C

Bulk Cable Weight: 61.016 Kg/Km

Max. Recommended Pulling Tension: 711.712 N

Min. Bend Radius/Minor Axis: 76.200 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Series Type:	Series 6

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75.000

Nom. Inductance:

Inductance (µH/m)

0.318257

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

53.1522

Nominal Velocity of Propagation:

VP (%)

83

Nominal Delay:

Delay (ns/m)

3.9372

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

91.868

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

29.529

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
5	1.6405
55	4.5934
211	8.5306
500	13.4521
750	16.7331
862	18.0455
1000	19.686
1450	25.5918
1800	28.2166
2250	32.1538
3000	37.0753

Max. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
5	2.19827
55	5.2496
211	9.41647
500	14.6989
750	18.3408

862	19.6204
1000	21.4577
1450	26.248
1800	28.8728
2250	32.81
3000	39.0439

Max. Operating Voltage - Non-UL:

Voltage
350 V RMS

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
950	2250	15
2250	3000	10

Sweep Test

Sweep Testing: 950 MHz - 3 GHz

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1839A 0101000	1,000 FT	44.000 LB	BLACK	C	#18 GIFHDLPE SH PVC W/MSG

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 10-17-2013

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.