



For more Information
please call

1-800-Belden1



General Description:

SO oil-resistant rubber jacket, 600V, 90°C, paper tape separator, smooth jacket, UL/CSA listed, color code: black, white, green.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
3	14	41x30	BC - Bare Copper

Total Number of Conductors: 3

Type of Cordage: SO

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
EPDM - Ethylene Propylene Diene Monomer Rubber	1.2192

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
Rubber	2.1844

Overall Cable

Overall Cabling Fillers: Jute

Overall Cabling Color Code Chart:

Color
Black
White
Green

Overall Cabling Separator Material: Paper Tape

Overall Nominal Diameter: 13.665 mm

Mechanical Characteristics (Overall)

Bulk Cable Weight: 239.600 Kg/Km

Min. Bend Radius/Minor Axis: 139.700 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: SO

CSA Specification: SO

EU Directive 2011/65/EU (ROHS II): Yes

19207 Portable Cordage - UL/CSA Types: S, SO, SJ

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Surface Printing (Overall)

Surface Printing: Surface Impression Printed

Electrical Characteristics (Overall)

Max. Operating Voltage - UL:

Voltage
600 V RMS

Max. Recommended Current:

Current
18 Amps per conductor @ 25°C
13 Amps per conductor @ 25°C over 50 ft.

Dielectric Withstand Voltage: 3000 V AC Applied For 1 Min.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
19207 010250	250 FT	43.500 LB	BLACK	C F	3 #14 EPDM NEO

Notes:

C = CRATE REEL PUT-UP.

F = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'

Revision Number: 2 Revision Date: 10-01-2012

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).