

METRIC MEASUREMENT VERSION

76205WS Multi-Conductor - 300V Foil/Spiral Shield, Continuous Flexing Data Applications Up to 6 Million Flex Life Cycles



For more Information
please call

1-800-Belden1

General Description:

24 AWG stranded (10x34) tinned copper conductors, PVC insulation, Aluminum/Polyester Foil Shield, Tinned copper spiral shield, 90% coverage, oil-resistant PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
5	24	10x34	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.254

Insulation Color Code Chart:

Number	Color
1	Black
2	Red
3	White
4	Green
5	Orange

Outer Shield

Outer Shield Material:

Layer #	Type	Outer Shield Material	Coverage (%)
1	Tape	Aluminum/Mylar	100.000
2	Serve	TC - Tinned Copper	90.000

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.016

Overall Cable

Overall Nominal Diameter: 5.715 mm

Mechanical Characteristics (Overall)

Bulk Cable Weight: 49.111 Kg/Km

Max. Recommended Pulling Tension: 92.078 N

Min. Bend Radius/Minor Axis: 45.720 mm

Min. Bend/Installation: 45.720 mm

Min. Bend Radius (Continuous Flexing): 45.720 mm

Flex Cycle Rating: 6 Million Flexes

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CM

CEC/C(UL) Specification: CMG

EU Directive 2011/65/EU (ROHS II): Yes

MII Order #39 (China RoHS): Yes

METRIC MEASUREMENT VERSION

76205WS Multi-Conductor - 300V Foil/Spiral Shield, Continuous Flexing Data Applications Up to 6 Million Flex Life Cycles

Customer Part Number Reference Specification: AWM/STYLE 10002, AWM/STYLE 2661, CSA AWM I/II A/B, EU Directive 2011/65/EU(RoHS2), REACH Regulation (EC 1907/2006), California Proposition 65

Flame Test

CSA Flame Test: FT4

Suitability

Suitability - Burial: Yes

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)
0.623

Nom. Capacitance Conductor to Conductor:

Freq. (MHz)	Capacitance (pF/m)
0.001	104.992

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
95.149

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
16.733

Max. Operating Voltage - UL:

Voltage
300V

Notes (Overall)

Notes: Temperature Range -10 to 105°C(static), +5 to 105°C (dynamic)

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
76205WS 008100	100 FT	4.800 LB	GRAY		24 AWG/5 COND MINI DIAMETER
76205WS 0081000	1,000 FT	35.000 LB	GRAY		24 AWG/5 COND MINI DIAMETER
76205WS 008500	500 FT	18.000 LB	GRAY		24 AWG/5 COND MINI DIAMETER

Revision Number: 0 Revision Date: 09-27-2017

© 2019 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.