

For more Information  
please call

1-800-Belden1



### General Description:

30 AWG stranded (7x38) .012" tinned copper conductors, plenum, foam FEP insulation, tinned copper "French braid" shield (95% coverage), Flamarrest® jacket.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
2	30	7x38	TC - Tinned Copper	0.3048

Total Number of Conductors: 2

#### Insulation

##### Insulation Material:

Insulation Trade Name	Insulation Material	Dia. (mm)
Teflon®	FFEP - Foam Fluorinated Ethylene Propylene	1.3462

#### Inner Shield

##### Inner Shield Material:

Type	Inner Shield Material	Coverage (%)
French Braid	TC - Tinned Copper	95.000

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride

#### Overall Cable

Overall Nominal Diameter: 2.718 x 5.461 mm

### Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +60°C

UL Temperature Rating: 60°C

Non-UL Temperature Rating: 60°C

Bulk Cable Weight: 29.764 Kg/Km

Max. Recommended Pulling Tension: 53.378 N

Min. Bend Radius/Minor Axis: 25.400 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP

CEC/C(UL) Specification: CMP

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy):	12/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

### Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

### Suitability

Suitability - Indoor:	Yes
-----------------------	-----

### Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	1807A

## Electrical Characteristics (Overall)

### Nom. Characteristic Impedance:

Impedance (Ohm)
75.000

### Nom. Inductance:

Inductance (µH/m)
0.318257

### Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)
56.7613

### Nominal Velocity of Propagation:

VP (%)
78

### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
328.1

### Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/km)
24.6075

### Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1	2.2967
5	5.5777
10	7.5463
30	13.4521
50	17.3893
100	24.9356
200	38.7158
400	57.7456
700	79.4002
900	91.868
1000	97.7738

### Max. Operating Voltage - UL:

Voltage
300 V RMS

### Max. Operating Voltage - Non-UL:

Voltage
---------

300 V RMS

### Notes (Overall)

**Notes:** Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7700A B591000	1,000 FT	21.000 LB	BLACK, MATTE	C	2#30 PPFASRVFLRSTPARA
7700A B59500	500 FT	11.500 LB	BLACK, MATTE		2#30 PFPA SRV FLRST PARA

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 2    Revision Date: 11-13-2013

© 2019 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).