



For more Information
please call

1-800-Belden1



General Description:

12mm Double Jacketed SMPTE 311M Studio Cable, 4 power conductors, SM fibers w/24 and 20 AWG stranded (7x32 and 19x32) TC conductors, PO insulation, TC braid shield (84% coverage), Belflex® jacket.

Usage (Overall)

Suitable Applications: SMPTE 311M Camera Cable

Twisted Pair

Physical Characteristics
Individual Shield

Multi Conductor

Physical Characteristics
Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (mm)
2	24	7x32	TC - Tinned Copper	0.610
4	20	19x32	TC - Tinned Copper	0.940

Insulation

Insulation Material:

Insulation Material	Dia. (mm)	AWG
PO - Polyolefin	1.575	20
PO - Polyolefin	1.219	24

Insulation Color Code Chart:

Number	Color	Description
1	Red	24 AWG
2	Gray	24 AWG
3	White	20 AWG
4	White	20 AWG
5	Black	20 AWG
6	Black	20 AWG

Individual Shield

Electrical Characteristics

Nom. Conductor DC Resistance:

Description	DCR @ 20°C (Ohm/km)
24 AWG	76.447
20 AWG	28.873

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
11.484

Fiber

Physical Characteristics

Fiber Type: Non-Dispersion Shifted, Single Mode/125/900 Micron

Number of Fibers: 2

Mode Field Diameter @ 1310nm: 9.5 +/-1 microns

Clad Diameter:	125 microns
Core-clad Concentricity Error:	< to 1 micron
Primary Coating Material:	Acrylate
Buffer Tube Diameter:	900 microns
Buffer Tube Material:	PVC - Polyvinyl Chloride

Buffer Tube Color Code Chart:

Number	Color
1	Blue
2	Yellow

Optical Characteristics

Maximum Attenuation @ 1310nm:	0.8 dB/km
--------------------------------------	-----------

Physical Characteristics (Overall)

Conductor

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	85.000

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Belflex®	PVC Blend - Polyvinyl Chloride Blend

Strength Member

Overall Strength Member Diameter:	.085
Strength Member Material:	302 Stainless Steel

Overall Cable

Overall Nominal Diameter:	11.989 mm
----------------------------------	-----------

Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +75°C
Bulk Cable Weight:	160.726 Kg/Km
Max. Recommended Pulling Tension:	2001.690 N
Min. Bend Radius/Minor Axis:	82.550 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Rating:	UL AWM Style 20907 (300V 60°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	SMPTE 311

Flame Test

UL Flame Test:	VW-1
-----------------------	------

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Sunlight Resistance:	Yes
Suggested Connectors:	SMPTE 304M Connectors

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	7804P
Non-Plenum Number:	7804C, 7804R, 7804WB

Electrical Characteristics (Overall)

Other Electrical Characteristic 1:	Auxillary Conductors: DC Loop Resistance - 30 Ohms/km nom. (9.1 Ohms/1000ft.) Min. Insulation Resistance - 10, 000 Megaohms x km Dielectric Strength - 1750 V RMS. Signal Conductors: DC Loop Resistance - 150 Ohms/km nom. (45.7 Ohms/1000 ft.) Insulation Resistance - 10, 000 Megaohms/1000 ft. Dielectric Strength: 1750 V RMS
------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Notes (Overall)

Notes: Bend Radius is based upon (FOTP-37) @ 20°C. Plenum version and other conductor counts/diameters available by special order.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7817A 010CUT	1 FT	0.131 LB	BLACK		COMPOSITE-SMPTE311M HDTV CABLE
7817A 0101000	1,000 FT	119.000 LB	BLACK		COMPOSITE-SMPTE311M HDTV CABLE

Revision Number: 0 Revision Date: 03-27-2015

© 2020 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.