

7951A Composite - Composite Data, Audio, Video, Security and Control Cable



For more Information
please call

1-800-Belden1



General Description:

Composite - (1)Cat 5 4-pair, 24 AWG unshielded plus (4) 18 AWG stranded (19x30) bare copper conductors, polyolefin Insulation on the pairs; PVC insulation on the conductors, overall F-R PVC jacket. Jacket sequentially marked.

Usage (Overall)

Suitable Applications:

Keypads, Control Panels, Touch Panel Controls, Home Theater, AV Equipment, Projectors, Screens, Window Treatments, Lighting, Security, Security Cameras, Home Automation, Energy Control

Twisted Pair

Physical Characteristics

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
4	24	Solid	BC - Bare Copper	0.508

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
PO - Polyolefin	0.914

Twisted Pair Color Code Chart:

Number	Color
1	White/Blue Stripe and Blue
2	White/Orange Stripe and Orange
3	White/Green Stripe and Green
4	White/Brown Stripe and Brown

Individual Shield

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (mm)
4.953

Outer Jacket Ripcord:

Yes

Outer Jacket Color Code Chart:

Color
Lt Green

Electrical Characteristics

Premise Cable Electricals:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. SRL (dB)	Fitted Imp. (Ohms)
1.0	2.000	62	N/A	23	100 ± 15%
4.0	4.100	53	N/A	23	100 ± 15%
8.0	5.800	48	N/A	23	100 ± 15%
10.0	6.500	47	N/A	23	100 ± 15%

7951A Composite - Composite Data, Audio, Video, Security and Control Cable

16.0	8.200	44	N/A	23	100 ± 15%
20.0	9.300	42	N/A	23	100 ± 15%
25.0	10.400	41	N/A	22	100 ± 15%
31.25	11.700	39	N/A	21	100 ± 15%
62.5	17.000	35	N/A	18	100 ± 15%
100	22.000	32	N/A	16	100 ± 15%

Multi Conductor

Physical Characteristics

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (mm)
4	18	19x30	BC - Bare Copper	1.118

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
PVC - Polyvinyl Chloride	1.676

Insulation Color Code Chart:

Number	Color
1	Red
2	White
3	Green
4	Black

Individual Shield

Electrical Characteristics

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
49.215

Nominal Velocity of Propagation:

VP (%)
70.000

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
30.776

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
4 Amps per conductor @ 25°C

Other Electrical Characteristic 1: Third party verified to TIA/EIA 568-B.2, Category 5

Physical Characteristics (Overall)

Conductor

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Ripcord: Yes

7951A Composite - Composite Data, Audio, Video, Security and Control Cable

Overall Cable

Overall Nominal Diameter: 10.338 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

Bulk Cable Weight: 110.127 Kg/Km

Max. Recommended Pulling Tension: 547.129 N

Min. Bend Radius/Minor Axis: 114.300 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR

CEC/C(UL) Specification: CMG

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Other Specification: NEMA WC-63/1. Category 5

Flame Test

UL Flame Test: UL1666 Riser

CSA Flame Test: FT4

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Max. Operating Voltage - UL:

Voltage
300 V RMS

Notes (Overall)

Notes: Overall jacket sequentially marked.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7951A 3371000	1,000 FT	84.000 LB	GREEN, LIGHT	C	COMPOSITE CABLE PVC
7951A 337500	500 FT	47.000 LB	GREEN, LIGHT	C	COMPOSITE CABLE PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 0 Revision Date: 09-10-2013

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications

7951A Composite - Composite Data, Audio, Video, Security and Control Cable

described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).