



For more Information  
please call

1-800-Belden1



### General Description:

Surveillance & CCTV Cable, RG59, Plenum-CMP-FHC 25/50, 20 AWG bare copper Foamed FEP core, 95% bare copper braid, FEP jacket

### Usage (Overall)

Suitable Applications: CCTV

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	20	Solid	BC - Bare Copper	0.8128

Total Number of Conductors: 1

#### Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Dia. (mm)
Teflon®	FFEP - Foam Fluorinated Ethylene Propylene	3.429

#### Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	95

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Teflon®	FEP - Fluorinated Ethylene Propylene

#### Overall Cable

Overall Nominal Diameter: 4.902 mm

### Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +200°C

UL Temperature Rating: 200°C

Bulk Cable Weight: 46.134 Kg/Km

Max. Recommended Pulling Tension: 231.306 N

Min. Bend Radius/Minor Axis: 44.450 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: Limited Combustible FHC 25/50 CMP

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	59/U
Series Type:	Series 59

### Flame Test

UL Flame Test:	UL723 (NFPA 255)
----------------	------------------

### Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

### Surface Printing (Overall)

Surface Printing:	"NEW GENERATION(R) BY BELDEN 7986LC RG-59 TYPE 1C20 200C E108998 (UL) LIMITED COMBUSTIBLE FHC 25/50 CMP OR C(UL) CMP (2 FT. 7 DIGIT SEQUENTIAL NUMBER) FEET"
-------------------	--

### Electrical Characteristics (Overall)

#### Nom. Characteristic Impedance:

Impedance (Ohm)

75

#### Nom. Inductance:

Inductance (µH/m)

0.318257

#### Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

52.8241

#### Nominal Velocity of Propagation:

VP (%)

84

#### Nominal Delay:

Delay (ns/m)

3.97001

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

32.81

#### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

8.2025

#### Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1	0.95149
3	1.90298
5	2.2967
8	2.85447
10	3.44505
50	5.9058
100	8.8587
200	12.7959
400	19.3579
700	27.8885
900	32.81

1000	35.1067
------	---------

**Max. Operating Voltage - UL:**

<b>Voltage</b>
300 V RMS

### Notes (Overall)

**Notes:** Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7986LC 0101000	1,000 FT	33.000 LB	BLACK	C	#20 FFEP BRD FEP
7986LC 010500	500 FT	17.000 LB	BLACK	C	#20 FFEP BRD FEP

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 2    Revision Date: 03-13-2013

© 2019 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).