

83653 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information
please call

1-800-Belden1



General Description:

18 AWG stranded (19x30) TC conductors, conductors cabled, plenum, FEP insulation, overall Beldfoil® (100% coverage) + TC braid shield (85% coverage), FEP jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
3	18	19x30	TC - Tinned Copper

Total Number of Conductors: 3

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
FEP - Fluorinated Ethylene Propylene	0.1778

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	85

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
FEP - Fluorinated Ethylene Propylene	0.3556

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White
3	Red

Overall Nominal Diameter: 4.572 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

Bulk Cable Weight: 63.993 Kg/Km

Max. Recommended Pulling Tension: 320.270 N

Min. Bend Radius/Minor Axis: 50.800 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP

NEC Articles: 800

CEC/C(UL) Specification: CMP

METRIC MEASUREMENT VERSION

83653 Multi-Conductor - Audio, Control and Instrumentation Cable

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: NFPA 262

CSA Flame Test: FT6

Suitability

Suitability - Indoor: Yes

Plenum/Non-Plenum

Plenum (Y/N): Yes

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)

0.406844

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

108.273

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

196.86

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

19.0298

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

12.7959

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Description	Current
10C temperature rise	5 Amps per conductor @ 25°C ambient

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
83653 002100	100 FT	5.300 LB	RED	C	3#18 FEP SH FEP
83653 0021000	1,000 FT	38.000 LB	RED	C	3#18 FEP SH FEP
83653 002500	500 FT	19.000 LB	RED	C	3#18 FEP SH FEP
83653 0025000	5,000 FT	180.000 LB	RED		3 #18 FEP SH FEP

Notes:

C = CRATE REEL PUT-UP.

83653 Multi-Conductor - Audio, Control and Instrumentation Cable

Revision Number: 2 Revision Date: 08-02-2013

© 2019 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).