

27122A Multi-Conductor - 600V Type TC Cable

For more Information
please call

1-800-Belden1



General Description:

12 AWG multi-conductor stranded (7x20) bare copper conductors, PVC/Nylon insulation, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
15	12	7x20	BC - Bare Copper

Total Number of Conductors: 15

Ground Wire

Ground Wire (Y/N): N

Insulation

Insulation Material:

Insulation Material
PVC/Nylon - Polyvinyl Chloride/Nylon

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.524

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red
3	Blue
4	Orange
5	Yellow
6	Brown
7	Red/Black
8	Blue/Black
9	Orange/Black
10	Yellow/Black
11	Brown/Black
12	Black/Red
13	Blue/Red
14	Orange/Red
15	Yellow/Red

Overall Nominal Diameter: 18.796 mm

Mechanical Characteristics (Overall)

Wet Temperature Range: -30°C To +75°C

27122A Multi-Conductor - 600V Type TC Cable

Dry Temperature Range:	-30°C To +90°C Dry
Bulk Cable Weight:	696.478 Kg/Km
Max. Recommended Pulling Tension:	4052.310 N
Min. Bend Radius/Minor Axis:	187.960 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	TC, NPLF
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	ICEA S-73-532, S-95-658, S-61-402

Flame Test

UL Flame Test:	UL1685 UL Loading
CSA Flame Test:	FT4
IEEE Flame Test:	1202
ICEA Flame Test:	T-29-520

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
5.41365

Max. Operating Voltage - UL:

Voltage
600 V RMS

Max. Recommended Current:

Current
16 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 1 Revision Date: 05-14-2007

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

27122A Multi-Conductor - 600V Type TC Cable

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.