

8443MN Multi-Conductor - SpaceMaker Audio, Control and Instrumentation Cable



For more Information
please call

1-800-Belden1



General Description:

22 AWG stranded (19x34) tinned copper conductors, conductors cabled, Polypropylene insulation, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
3	22	19x34	TC - Tinned Copper

Total Number of Conductors: 3

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.254

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.406

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White
3	Red

Overall Nominal Diameter: 3.556 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

Bulk Cable Weight: 23.811 Kg/Km

Max. Recommended Pulling Tension: 66.723 N

Min. Bend/Installation: 14.224 mm

Min. Bend Radius (Continuous Flexing): 35.560 mm

Flex Cycle Rating: 1 Million Flexes

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

METRIC MEASUREMENT VERSION

8443MN Multi-Conductor - SpaceMaker Audio, Control and Instrumentation Cable

EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	UL Style AWM 2937 (300V 80C), NFPA 79

Flame Test

CSA Flame Test:	FT2
IEEE Flame Test:	1202

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Tolerance (Ohms)
51

Nom. Inductance:

Inductance (µH/m)
0.102

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
54.465

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
48.887

Max. Operating Voltage - UL:

Voltage
300V RMS

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8443MN 004100	100 FT	2.700 LB	YELLOW		3 #22 PO PVC
8443MN 0041000	1,000 FT	14.000 LB	YELLOW		3 #22 PO PVC
8443MN 006100	100 FT	2.700 LB	BLUE, LIGHT		3 #22 PO PVC
8443MN 0061000	1,000 FT	14.000 LB	BLUE, LIGHT		3 #22 PO PVC
8443MN 008100	100 FT	2.700 LB	GRAY		3 #22 PO PVC
8443MN 0081000	1,000 FT	14.000 LB	GRAY		3 #22 PO PVC

Revision Number: 0 Revision Date: 09-29-2016

© 2020 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

8443MN Multi-Conductor - SpaceMaker Audio, Control and Instrumentation Cable