

85231 Multi-Conductor - Control and Instrumentation Cable, 2 Conductors Cabled



For more Information
please call

1-800-Belden1



General Description:

16 AWG stranded (19x29) TC conductors, conductors cabled, Tefzel® insulation, drain wire, overall Beldfoil® Aluminum-Kapton® Shield (100% coverage), Tefzel® jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	16	19x29	TC - Tinned Copper

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (mm)
Tefzel®	ETFE - Ethylene Tetrafluoroethylene	0.3429

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Tape	Aluminum-Kapton® Foil	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
18	Stranded	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (mm)
Tefzel®	ETFE - Ethylene Tetrafluoroethylene	0.508

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red

Overall Nominal Diameter: 5.334 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -60°C To +150°C

Non-UL Temperature Rating: 150°C

Bulk Cable Weight: 50.599 Kg/Km

Max. Recommended Pulling Tension: 266.892 N

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

METRIC MEASUREMENT VERSION

85231 Multi-Conductor - Control and Instrumentation Cable, 2 Conductors Cabled

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	NEMA HP3

Flame Test

UL Flame Test:	VW-1
----------------	------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)
0.541365

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
144.364

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
259.199

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
14.0099

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
6.5 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
85231 3681000	1,000 FT	38.000 LB	CLEAR, TRANSPARENT	C	2#16 TEFZEL FS TEFZEL
85231 368500	500 FT	19.000 LB	CLEAR, TRANSPARENT	C	2#16 TEFZEL FS TEFZEL

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 08-14-2012

© 2019 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and

METRIC MEASUREMENT VERSION

85231 Multi-Conductor - Control and Instrumentation Cable, 2 Conductors Cabled

the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).