

8724 Multi-Conductor - Special Audio, Communication and Instrumentation Cable



For more Information
please call

1-800-Belden1



General Description:

22 AWG stranded (7x30) tinned copper conductors, polypropylene insulation, one pair Beldfoil® shielded (100% coverage), stranded tinned copper drain wire, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
2	22	7x30	TC - Tinned Copper	0.762

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
PP - Polypropylene	1.168

Inner Shield

Inner Shield Material:

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
1st Pair	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2nd Pair			Unshielded	

Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Stranding: 7x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.4826

Overall Cable

Overall Nominal Diameter: 4.191 mm

Pair

Pair Color Code Chart:

Number	Color
1	Shielded Black & Red
2	Unshielded Green & White

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

UL Temperature Rating: 60°C

Non-UL Temperature Rating: 80°C

Bulk Cable Weight: 29.764 Kg/Km

Max. Recommended Pulling Tension: 161.914 N

8724 Multi-Conductor - Special Audio, Communication and Instrumentation Cable

Min. Bend Radius/Minor Axis:	44.450 mm
------------------------------	-----------

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

48

Nom. Inductance:

Inductance (µH/m)

0.55777

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

111.554

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

219.827

Nominal Velocity of Propagation:

VP (%)

66

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

49.215

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 55.777 Ohm/km

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

2.3 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8724 060U1000	1,000 FT	21.000 LB	CHROME		2#22 FS PP,2#22 PP PVC

METRIC MEASUREMENT VERSION

8724 Multi-Conductor - Special Audio, Communication and Instrumentation Cable

8724 060Z1000	1,000 FT	21.000 LB	CHROME		2#22 FS PP,2#22 PP PVC
8724 0601000	1,000 FT	21.000 LB	CHROME	C	2#22FS PP,2#22 PP PVC
8724 0605000	5,000 FT	105.000 LB	CHROME		2#22 FS PP,2#22 PP PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 09-06-2012

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).