



For more Information
please call

1-800-Belden1



General Description:

16 AWG multi-conductor stranded (7x24) bare copper conductors, PVC/Nylon insulation, overall Beldfoil® shield (100% coverage) with drain wire, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
3	16	7x24	BC - Bare Copper

Total Number of Conductors: 3

Ground Wire

Ground Wire (Y/N): N

Insulation

Insulation Material:

Insulation Material
PVC/Nylon - Polyvinyl Chloride/Nylon

Insulation Color Code Chart:

Number	Color
1	Black
2	Red
3	Blue

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100.000

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
16	7x24	TC	Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.194

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Lay Length & Direction:

Length (mm)	Twists (twist/m)
69.849725	14.4364

Overall Nominal Diameter: 8.128 mm

Mechanical Characteristics (Overall)

Wet Temperature Range: -30°C To +75°C

Dry Temperature Range: -30°C To +90°C

28331AS Multi-Conductor - 600V Type TC-ER Cable

Bulk Cable Weight:	81.851 Kg/Km
Max. Recommended Pulling Tension:	578.266 N
Min. Bend Radius/Minor Axis:	81.280 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	NPLF, TC-ER
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	ICEA S-73-532 (WC57), S-95-658, S-61-402

Flame Test

UL Flame Test:	UL1685 UL Loading
C(UL) Flame Test:	FT4
IEEE Flame Test:	1202

Plenum/Non-Plenum

Plenum (Y/N):	No
----------------------	----

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

13.7802

Max. Operating Voltage - Other:

Voltage

600 V RMS

Max. Recommended Current:

Current

7 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
28331AS 0105000	5,000 FT	335.000 LB	BLACK	C Z	3 #16 PVC/NYL FS PVC
28331AS01010000	10,000 FT	690.000 LB	BLACK	C Z	3 #16 PVC/NYL FS PVC

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 1 Revision Date: 05-30-2017

© 2018 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express,

28331AS Multi-Conductor - 600V Type TC-ER Cable

statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).