

For more Information  
please call

1-800-Belden1



## General Description:

100 ohm, 20 AWG stranded (7x28) .037" one tinned/ one bare copper conductors, polyethylene insulation, Duofoil® + TC braid shield (95% coverage), high-density polyethylene jacket.

## Physical Characteristics (Overall)

### Conductor

#### AWG:

# Pairs	AWG	Stranding	Conductor Material
1	20	7x28	TC - Tinned Copper
			BC - Bare Copper

Total Number of Conductors: 2

### Insulation

#### Insulation Material:

Insulation Material	Wall Thickness (mm)
PE - Polyethylene	0.610

### Inner Jacket

#### Inner Jacket Material:

Inner Jacket Material	Nom Wall (mm)	Nom. Dia. (mm)
PE - Polyethylene	0.889	5.994

### Outer Shield

#### Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Outer Shield Flooding Grease: Polyethylene Grease

### Outer Jacket

#### Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
HDPE - High Density Polyethylene	0.864

### Overall Cable

Overall Nominal Diameter: 8.382 mm

### Pair

#### Pair Color Code Chart:

Number	Color
1	Natural & Natural

## Mechanical Characteristics (Overall)

Operating Temperature Range: -55°C To +80°C

Bulk Cable Weight: 92.268 Kg/Km

Max. Recommended Pulling Tension: 511.543 N

Min. Bend Radius/Minor Axis: 88.900 mm

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

### Suitability

Suitability - Burial:	Yes
-----------------------	-----

### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Electrical Characteristics (Overall)

### Nom. Characteristic Impedance:

Impedance (Ohm)

100

### Nom. Inductance:

Inductance (µH/m)

0.508555

### Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

47.5745

### Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

75.463

### Nominal Velocity of Propagation:

VP (%)

66

### Nominal Delay:

Delay (ns/m)

5.05274

### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

31.1695

### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

6.562

### Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100m)

1	1.3124
10	3.6091
50	8.2025
100	13.4521
200	20.9984
400	33.4662

**Max. Operating Voltage - Non-UL:**

<b>Voltage</b>
600 V RMS

**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9815 0101000	1,000 FT	69.000 LB	BLACK	C	BRAID TW PR #20 PE PE BRD PE
9815 010500	500 FT	34.500 LB	BLACK		BRAID TW PR #20 PE PE BRD PE

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 3    Revision Date: 04-04-2017

© 2019 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).