



For more Information
please call

1-800-Belden1



General Description:

6 AWG stranded (7x14) bare copper circuit conductors plus (3) - 12 AWG stranded (7x20) symmetrical bare copper ground wires, XLPE insulation, two spiral copper tape shields (100% Coverage), sun- and oil-resistant PVC jacket.

Usage (Overall)

Suitable Applications: AC Motor Drives, VFD, Variable Frequency Drive

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
3	6	7x14	BC - Bare Copper

Total Number of Conductors: 3

Ground Wire

Ground Wire (Y/N): Y

Ground Wire AWG: 12

Ground Wire Stranding: 7x20

Ground Wire Conductor Material: BC - Bare Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
XLPE - Cross Linked Polyethylene	1.168

Insulation Color Code Chart:

Number	Color
1	Black and Numbered 1
2	Black and Numbered 2
3	Black and Numbered 3

Outer Shield

Outer Shield Material:

Layer #	Type	Outer Shield Material	Coverage (%)
1	Tape	Spiral Copper	100.000
2	Tape	Spiral Copper	100.000

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.600

Overall Cable

Overall Nominal Diameter: 18.390 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +90°C

UL Temperature Rating:	90°C Wet/Dry
Bulk Cable Weight:	696.478 Kg/Km
Max. Recommended Pulling Tension:	4070.103 N
Min. Bend Radius/Minor Axis:	185.420 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	TC-ER, XHHW-2 Singles
NEC Articles:	336 - ER
CSA Specification:	1000 V AWM I/II A/B
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	08/17/2007
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
PMSHA Specification:	P-07-KA070003-MSHA

Flame Test

UL Flame Test:	UL1685 UL Loading, VW-1 (Singles)
CSA Flame Test:	FT4
IEEE Flame Test:	1202

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Burial:	Yes
Sunlight Resistance:	Yes
Oil Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
1.345

Max. Operating Voltage - UL:

Voltage	Description
600 V RMS	NEC Type TC

Max. Operating Voltage - Other:

Voltage	Description
1000 V RMS	CSA AWM I/II A/B

Max. Recommended Current:

Description	Current
Per NEC	75 Amps per conductor @ 25°

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
29525C 0101000	1,000 FT	555.000 LB	BLACK		3 #6XLPE+3 #12 GRD CU TAPE PVC
29525C 0103500	3,500 FT	1,781.500 LB	BLACK		3 #6XLPE+3 #12 GRD CU TAPE PVC
29525C 0105000	5,000 FT	2,495.000 LB	BLACK		3 #6XLPE+3 #12 GRD CU TAPE PVC

Revision Number: 2 Revision Date: 08-31-2017

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).