

For more Information  
please call

1-800-Belden1



## General Description:

Neoprene insulation has good heat aging characteristics and is an excellent low-cost motor lead wire. It may be considered for use in hazardous locations and is being used in explosion-proof motors recognized by UL.

## Physical Characteristics (Overall)

### Conductor

#### AWG:

# Conductors	AWG	Stranding	Conductor Material
1	10	65x28	TC - Tinned Copper

Total Number of Conductors: 1

### Insulation

#### Insulation Material:

Insulation Material	Wall Thickness (mm)
Neoprene	1.143

### Overall Insulation

#### Overall Cable

Overall Nominal Diameter: 5.309 mm

## Mechanical Characteristics (Overall)

Non-UL Temperature Rating: 90°C

Recommended Maximum Baking Cycles: 24 Hours @ 300°F (149°C) ~ 8 Hours @ 325°F (163°C) ~ 15 Minutes @ 450°F (232°C)

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

UL AWM Style: 3046

UL Rating: 600 V, 90°C

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

### Plenum/Non-Plenum

Plenum (Y/N): No

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

## METRIC MEASUREMENT VERSION

### 31510 Hook-up/Lead - UL AWM Style 3046

31510 0102000	2,000 FT	106.000 LB	BLACK	#10 STR CR 90C 600V
---------------	----------	------------	-------	---------------------

Revision Number: 1    Revision Date: 05-14-2007

© 2019 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.