

5100UP Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled



For more Information
please call

1-800-Belden1



General Description:

Commercial Audio Cable, Rated-CL3, 2-14 AWG highly flexible stranded bare copper conductors with PVC insulation, PVC jacket with ripcord

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	14	42x30	Bare High-Conductivity ETP Copper

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.508

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.457

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Lay Length & Direction:

Length (mm)	Twists (twist/m)
88.89965	11.1554

Overall Cabling Color Code Chart:

Color
Black
White

Overall Nominal Diameter: 6.756 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 58.040 Kg/Km

Max. Recommended Pulling Tension: 485.743 N

Min. Bend Radius/Minor Axis: 66.675 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

METRIC MEASUREMENT VERSION

5100UP Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled

NEC/(UL) Specification:	CL3
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)
0.55777

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
95.149

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
7.94002

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
22 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5100UP 005U1000	1,000 FT	43.000 LB	GREEN, DARK		2 #14 PVC FRPVC
5100UP 005U500	500 FT	22.000 LB	GREEN, DARK		2 #14 PVC FRPVC
5100UP 0051000	1,000 FT	45.000 LB	GREEN, DARK		2 #14 PVC FRPVC
5100UP 005500	500 FT	23.500 LB	GREEN, DARK		2 #14 PVC FRPVC
5100UP 008U1000	1,000 FT	43.000 LB	GRAY		2 #14 PVC FRPVC
5100UP 008U500	500 FT	22.000 LB	GRAY		2 #14 PVC FRPVC
5100UP 0081000	1,000 FT	45.000 LB	GRAY	C	2 #14 PVC FRPVC
5100UP 009U1000	1,000 FT	43.000 LB	WHITE		2 #14 PVC FRPVC
5100UP 009U500	500 FT	22.000 LB	WHITE		2 #14 PVC FRPVC
5100UP 0091000	1,000 FT	45.000 LB	WHITE		2 #14 PVC FRPVC
5100UP 009500	500 FT	23.500 LB	WHITE		2 #14 PVC FRPVC
5100UP 010U1000	1,000 FT	43.000 LB	BLACK		2 #14 PVC FRPVC
5100UP 010U500	500 FT	22.000 LB	BLACK		2 #14 PVC FRPVC
5100UP 010Z1000	1,000 FT	46.000 LB	BLACK		2 #14 PVC FRPVC
5100UP 0101000	1,000 FT	45.000 LB	BLACK	C	2 #14 PVC FRPVC
5100UP 010500	500 FT	23.500 LB	BLACK		2 #14 PVC FRPVC

Notes:

C = CRATE REEL PUT-UP.

5100UP Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled

Revision Number: 1 Revision Date: 03-13-2013

© 2019 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).