

For more Information  
please call

1-800-Belden1



### General Description:

Thermostat & Control Cable, Riser-CMR, 2-18 AWG stranded tinned copper pairs with foamed polyolefin insulation, Individually Beldfoil® shielded and PVC jacket with ripcord

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Pairs	AWG	Stranding	Conductor Material
2	18	7x26	TC - Tinned Copper

Total Number of Conductors: 4

#### Insulation

##### Insulation Material:

Insulation Trade Name	Insulation Material
Datalene®	FHDPE - Foam High Density Polyethylene

#### Inner Shield

##### Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100.000

##### Inner Shield Drain Wire AWG:

AWG	Stranding	Conductor Material
18	7x26	TC - tinned copper

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

#### Overall Cable

Overall Nominal Diameter: 7.823 mm

#### Pair

##### Pair Color Code Chart:

Number	Color
1	Black & White
2	Green & Red

### Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +75°C
UL Temperature Rating:	75°C
Bulk Cable Weight:	80.363 Kg/Km
Max. Recommended Pulling Tension:	596.059 N
Min. Bend Radius/Minor Axis:	78.740 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

## 5341PT Multi-Conductor - Thermostat & Control

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	02/01/2006
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

### Flame Test

UL Flame Test:	UL1666 Riser
C(UL) Flame Test:	FT4

### Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6341PT

## Electrical Characteristics (Overall)

### Nom. Inductance:

Inductance (µH/m)
0.68901

### Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
55.449

### Nominal Velocity of Propagation:

VP (%)
78

### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
21.6546

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 17.389 Ohm/km

### Max. Operating Voltage - UL:

Voltage
300 V RMS

### Max. Recommended Current:

Current
8.1 Amps per conductor @ 25°C

### Input/Unfitted Impedance:

Impedance (Ohm)
100.000

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5341PT 0011000	1,000 FT	58.000 LB	BROWN	C	2 FS PR #18 FHDPE FRPVC

### Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1    Revision Date: 08-14-2013

© 2019 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).