



For more Information  
please call

1-800-Belden1



### General Description:

Security & Commercial Audio Cable, Plenum-CL2P 3-14 AWG stranded bare copper conductors with Flamarrest® insulation, Flamarrest® jacket with ripcord

### Usage (Overall)

**Suitable Applications:** Intercom/PA Systems, Sound/Audio Systems

### Physical Characteristics (Overall)

#### Conductor

**AWG:**

# Conductors	AWG	Stranding	Conductor Material
3	14	19x27	BC - Bare Copper

**Total Number of Conductors:** 3

#### Insulation

**Insulation Material:**

Insulation Trade Name	Insulation Material	Wall Thickness (mm)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	0.254

#### Outer Shield

**Outer Shield Material:**

Outer Shield Material
Unshielded

#### Outer Jacket

**Outer Jacket Material:**

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (mm)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	0.381

**Outer Jacket Ripcord:** Yes

#### Overall Cable

**Overall Cabling Lay Length & Direction:**

Length (mm)
101.5996

**Overall Cabling Color Code Chart:**

Number	Color
1	Black
2	White
3	Red

**Overall Nominal Diameter:** 5.690 mm

### Mechanical Characteristics (Overall)

**Operating Temperature Range:** 0°C To +75°C

**UL Temperature Rating:** 75°C

**Bulk Cable Weight:** 78.726 Kg/Km

**Max. Recommended Pulling Tension:** 633.869 N

## 6101UE Multi-Conductor - Commercial Audio Systems

Min. Bend Radius/Minor Axis: 57.150 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CL2P

NEC Articles: 725

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

#### Flame Test

UL Flame Test: NFPA 262

#### Plenum/Non-Plenum

Plenum (Y/N): Yes

Non-Plenum Number: 5101UE

### Electrical Characteristics (Overall)

#### Nom. Inductance:

Inductance (µH/m)

0.49215

#### Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

108.273

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

8.30093

#### Max. Operating Voltage - UL:

Voltage

150 V RMS

#### Max. Recommended Current:

Current

8 Amps per conductor @ 25°C

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
6101UE 8771000	1,000 FT	53.000 LB	NATURAL	C	3 #14 FLRST FLRST

#### Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2    Revision Date: 03-22-2013

© 2019 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

## **6101UE Multi-Conductor - Commercial Audio Systems**

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).